

Spring-loaded test probe


GKS-112 259 060 A 0605 MD

Item GKS-112-2231



ingun[®]

Partner for Future Technology



General data

Product group:	ICT / FCT (in-circuit test and function test)
Sub-product group:	Flying probe
Series:	GKS-112 MD screw-in
Grid:	2.54 mm [100 mil]
Contacting from:	Pad, pin
Magnetic:	Yes
Installation type:	Screw-in
Quick-exchange system:	Yes
Adjustable installation height:	No
Non-rotating:	No
Screw-in torque:	3 - 5 cNm [.265 - .442 lbf·in]
Compatible receptacle(s):	KS-112 M
Min. temperature:	- 40 °C [- 104 °F]
Max. temperature:	+ 80 °C [+ 176 °F]
RoHS-compliant:	RoHS-3;6a;6c

Electrical data

Current load capacity / rated current:	5 A
Typical resistance (R _i):	<20 mOhm

Mechanical data

Total length:	43.5 mm [1.71 in]
Barrel diameter:	1.65 mm [.064 in]
Maximum stroke:	8 mm [.314 in]
Spring pre-load:	0.2 N [.719 ozf]
Collar height:	05
Spring force at working stroke:	0.6 N [2.15 ozf]
Recommended working stroke:	4 mm [.157 in]

Tip style data

Tip style:	59 flexi needle, self-cleaning, special length
Tip diameter:	0.6 mm [.023 in]
Tip style surface:	A gold
Tip style material:	2 steel

Spring-loaded test probe


GKS-112 259 060 A 0605 MD

Item GKS-112-2231



ingun[®]

Partner for Future Technology



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 02/24_GB

Learn more about
ICT/FCT Test probes



ICT/FCT TEST PROBES

ingun.com