



DK 0100 B

IP
66

2.5 mm²

- without terminals
- Dimensions H x W x D: 84 x 84 x 55 mm
- With elastic membranes, which can be removed for cable entry via cable glands

ELECTRICAL PROPERTIES

Rated insulation voltage: $U_i = 1000\text{ V}$

CONNECTION DATA

CABLE ENTRIES

Cable entries:

Number of cable en-tries	Type of cable entry	Size of the metric knock-outs	Sealing range of the cable entry	Location of cable entry
4	elastic mem-branes	M20	6 mm - 15 mm	wall
3	elastic mem-branes	M16	6 mm - 13 mm	wall
1	elastic mem-branes	without	6 mm - 13 mm	bottom

MECHANICAL PROPERTIES

Type of lid fastening:	Quick locking: Opening and closing by quarter turn, locked position well visible (open - locked)
Delivered accessories:	External brackets, sealing plug
IP degree of protection:	IP66
Impact strength:	IK07
Sealable without accessories:	Yes

AMBIENT CONDITIONS

Application area:	Indoor installation
Maximum ambient temperature 24 h:	35 °C
Ambient temperature:	-25 °C up to +40 °C
Relative humidity:	≤ 50 % at 40 °C, ≤ 100 % at 25 °C

MATERIAL PROPERTIES

Material:	Polypropylene
Glow wire test according to IEC 60695-2-11:	750 °C
UL 94:	V-2
Temperature resistance:	-25 °C up to +80 °C
Halogen-free:	Yes
Silicone-free:	Yes

DIMENSIONS

Height:	84 mm
Width:	84 mm
Depth:	55 mm
Net weight:	0.0853 kg
Mounting height:	65 mm
Mounting width:	65 mm
Mounting depth:	40 mm

COLOURS

Colour:	Black, similar to RAL 9011
---------	----------------------------

CERTIFICATES

conforming to the standards:	DIN EN 60670-1/-22, IEC 60670-1/-22
------------------------------	-------------------------------------

Certificates:

Type of certificate	Certificate number
VDE	40049684

SALES DATA

Product number:	62000441
EAN:	4012591161523
Pack unit:	5
Customs tariff number:	85369010
ETIM class:	DYNAMIC: EC002600 - Box/housing for surface mounting on the wall/ceiling ETIM-8.0: EC002600 - Box/housing for surface mounting on the wall/ceiling ETIM-7.0: EC002600 - Box/housing for surface mounting on the wall/ceiling ETIM-6.0: EC002600 - Box/housing for surface mounting on the wall/ceiling ETIM-5.0: EC002600 - Box/housing for surface mounting on the wall/ceiling ETIM-4.0: EC002600 - Box/housing for surface mounting on the wall/ceiling

NOTE

When using the sealing plugs supplied, the specified protection class is not changed.

TENDER TEXT

Kabelabzweigkästen nach IEC 60670-22 mit heraustrennbaren, elastischen Dichtmembranen. Geeignet für Innenräume und geschützte Installation im Freien nach DIN VDE 0100, Teil 737. Für Umgebungstemperatur maximal +40 °C und minimal -25 °C, bei relativer Luftfeuchte 50 % bei +40 °C oder 100 % bei +25 °C. Werkstoff Temperaturbeständigkeit von -25 °C bis +70 °C, Brennverhalten nach VDE 0471, Teil 2 - Glühdrahtprüfung 750 °C, UL Subject 94 V-2. Schutzart nach IEC 60529: IP 66. Bemessungsisolationsspannung 1000 V. Werkstoff: Thermoplast, halogen- und silikonfrei. Farbe: schwarz, RAL 9011. Deckelbefestigung mit Schnellverschluss, ohne Zubehör plombierbar. Steckbare Außenlaschen zur Wandmontage im Lieferumfang enthalten. Fabrikat: HENSEL ENYCASE DK., Nennquerschnitt: 2,5 mm², Abmessungen HxBxT 84 x 84 x 55 mm

DRAWINGS

