



RATING:10(4)A 125/250V~T55 (cURus/ENEC15)
DIELECTRIC VOLTAGE-WITHSTAND:1,500VAC FOR 1 MINUTE
INSULATION RESISTANCE:DC 500V 100MΩ (MIN.)
CONTACT RESISTANCE:20mΩ INITIAL (MAX.)
WATERPROOF GRADE:IP68



X(PANEL THICKNESS)	Y(CUTOUT DIMENSION)	Z(CUTOUT DIMENSION)
0.75~1.25mm	19.2 ^{+0.1} ₋₀ mm	12.9 ^{+0.15} ₀ mm
1.25~2mm	19.4 ^{+0.1} ₋₀ mm	12.9 ^{+0.15} ₀ mm
2~3mm	19.8 ^{+0.1} ₋₀ mm	12.9 ^{+0.15} ₀ mm

PANEL CUTOUT DIMENSION TABLE



NOTE: TOLERANCES UNLESS OTHERWISE SPECIFIED:±.012/0.3 (in/mm)

REVISION	DESCRIPTION	REVISED BY	TOLERANCES		ANGLE $\frac{1}{2}^\circ$			UNIT	mm	PART NAME	DWG NO
④			DRAWN BY	楊偉韶	DESIGNED BY	蔡劍	SCALE	2/1		MR2 SPEC DRAWING	S8399A
③			CHECKED BY		APPROVED BY		DATE	2021.03.26	PART NO	MR2-111C2N-NBBP-39NC	
② 2021.03.26	首次出圖	楊偉韶									