




GO TO PRODUCT

- Robust test probes with distinctive collar (stop) on the barrel
- Optimum adjustment of the stroke ratios in the test fixture: The collar is available in different heights, which, in combination with the receptacles, allows a range of installation heights
- Stainless steel versions for temperatures from -100 °C up to +200 °C available



1:1



### General data

|                                 |                                               |
|---------------------------------|-----------------------------------------------|
| Product group:                  | ICT / FCT (in-circuit test and function test) |
| Sub-product group:              | Metric standard                               |
| Series:                         | GKS-113                                       |
| Grid:                           | 4 mm [157 mil]                                |
| Contacting from:                | Pad, pin, posts                               |
| Magnetic:                       | Yes                                           |
| Installation type:              | Plug-in                                       |
| Quick-exchange system:          | Yes                                           |
| Adjustable installation height: | No                                            |
| Non-rotating:                   | No                                            |
| Compatible receptacle(s):       | KS-113, KS-113 23                             |
| Min. temperature:               | - 40 °C [- 104 °F]                            |
| Max. temperature:               | + 80 °C [+ 176 °F]                            |
| RoHS-compliant:                 | RoHS-3;6a;6c                                  |

### Electrical data

|                                        |          |
|----------------------------------------|----------|
| Current load capacity / rated current: | 5 A      |
| Typical resistance (Ri):               | <30 mOhm |

### Mechanical data

|                                 |                   |
|---------------------------------|-------------------|
| Total length:                   | 35.3 mm [1.38 in] |
| Barrel diameter:                | 2.65 mm [.104 in] |
| Maximum stroke:                 | 5.3 mm [.208 in]  |
| Spring pre-load:                | 0.8 N [2.87 ozf]  |
| Collar height:                  | 10                |
| Spring force at working stroke: | 3 N [10.7 ozf]    |
| Recommended working stroke:     | 4 mm [1.57 in]    |

### Tip style data

|                     |                                 |
|---------------------|---------------------------------|
| Tip style:          | 14 4-point crown, self-cleaning |
| Tip diameter:       | 1.4 mm [.055 in]                |
| Tip style surface:  | R rhodium                       |
| Tip style material: | 2 steel                         |

# Test Probe


## GKS-113 214 140 R 3010

Item GKS-113-0759



**ingun**<sup>®</sup>

Partner for Future Technology



### INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162  
78467, Constance, Germany  
Phone +49 7531 8105-0  
Customer hotline +49 7531 8105-888  
Fax +49 7531 8105-65  
info@ingun.com



Prices and delivery times on request.  
Technical changes reserved. 03/24\_GB

Learn more about  
ICT/FCT Test probes



ICT/FCT TEST PROBES

ingun.com