

REL-IR-BL/L-115AC/4X21 - Single relay



1109564

<https://www.phoenixcontact.com/gb/products/1109564>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in industrial relay in basic design with power contacts, 4 changeover contacts, test button, status LED, mechanical switch position indicator, input voltage: 115 V AC

Commercial data

Item number	1109564
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	CKF947
Product key	CKF947
GTIN	4063151021535
Weight per piece (including packing)	31.344 g
Weight per piece (excluding packing)	31.344 g
Customs tariff number	85364900
Country of origin	AT

REL-IR-BL/L-115AC/4X21 - Single relay



1109564

<https://www.phoenixcontact.com/gb/products/1109564>

Technical data

Notes

General	Do not connect adjacent channels to SELV/ PELV and voltages dangerous to the touch.
General	The outputs are not suitable for switching different outer conductors.
General	Do not use to separate SELV / PELV circuits from other circuits, because safe isolation is not guaranteed.

Product properties

Product type	Single relay
Operating mode	100% operating factor
Mechanical service life	2x 10 ⁷ cycles

Insulation characteristics

Insulation	Basic insulation
------------	------------------

Insulation characteristics: Air clearances and creepage distances between coil and contact side

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

Electrical properties

Service life electrical	see diagram
Maximum power dissipation for nominal condition	1 W
Test voltage (Winding/contact)	2.5 kV _{rms} (50 Hz, 1 min., winding/contact)
Test voltage (Changeover contact/changeover contact)	2 kV _{rms} (50 Hz, 1 min., changeover contact/changeover contact)

Air clearances and creepage distances between coil and contact side

Rated insulation voltage	250 V AC
Rated surge voltage	5 kV

Input data

Coil side

Nominal input voltage U _N	115 V AC
Input voltage range	92 V AC ... 189.8 V AC (20 °C)
Mains frequency	50/60 Hz
Drive and function	monostable
Drive (polarity)	non-polarized
Typical input current at U _N	9.2 mA (50 Hz)
Typical response time	5 ms ... 15 ms
Typical release time range	5 ms ... 20 ms
Coil voltage	115 V AC
Status display	Yellow LED

REL-IR-BL/L-115AC/4X21 - Single relay



1109564

<https://www.phoenixcontact.com/gb/products/1109564>

Coil resistance	4.8 k Ω $\pm$ 12 %
-----------------	---------------------------

Output data

Switching

Contact switching type	4 changeover contacts
Type of switch contact	Single contact
Contact material	AgNi
Maximum switching voltage	250 V AC/DC
Minimum switching voltage	12 V (10 mA)
Limiting continuous current	6 A
Maximum inrush current	12 A (20 ms, N/O contacts)
Min. switching current	10 mA (12 V)
Interrupting rating (ohmic load) max.	144 W (24 V DC)
	130 W (48 V DC)
	90 W (60 V DC)
	66 W (110 V DC)
	88 W (220 V DC)
	1500 VA (250 V AC)
Switching capacity min.	120 mW

Connection data

Connection method	Plug-in connection
-------------------	--------------------

Dimensions

Width	22.5 mm
Height	28 mm
Depth	35.5 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	RT II
Degree of protection (Installation location)	$\geq$ IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Altitude	$\leq$ 2000 m

Standards and regulations

Air clearances and creepage distances between coil and contact side

Standards/regulations	EN 61810-1
-----------------------	------------

Mounting

Mounting type	Plug-in mounting
Assembly instructions	in rows with zero spacing

REL-IR-BL/L-115AC/4X21 - Single relay




1109564

<https://www.phoenixcontact.com/gb/products/1109564>

Mounting position	any
-------------------	-----

Drawings


Diagram



Interrupting rating

1109564

<https://www.phoenixcontact.com/gb/products/1109564>




Permissible humidity for operation and storage.

The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures $\leq 0^\circ\text{C}$ must be prevented


Area B: Condensation at ambient temperatures $> 0^\circ\text{C}$ must be prevented

On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature $\leq 25^\circ\text{C}$.




Operating voltage range

Diagram



Service life reduction factor



Electrical service life

REL-IR-BL/L-115AC/4X21 - Single relay



1109564

<https://www.phoenixcontact.com/gb/products/1109564>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1109564>



cUL Recognized
Approval ID: FILE E 228652



UL Recognized
Approval ID: FILE E 228652

cULus Recognized

REL-IR-BL/L-115AC/4X21 - Single relay



1109564

<https://www.phoenixcontact.com/gb/products/1109564>

Classifications

ECLASS

ECLASS-11.0	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601

ETIM

ETIM 8.0	EC001437
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

REL-IR-BL/L-115AC/4X21 - Single relay



1109564

<https://www.phoenixcontact.com/gb/products/1109564>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

REL-IR-BL/L-115AC/4X21 - Single relay



1109564

<https://www.phoenixcontact.com/gb/products/1109564>

Mandatory accessories

ECOR-2-BSC2-RT/4X21 - Relay base

2908214

<https://www.phoenixcontact.com/gb/products/2908214>

ECOR-2 relay base, for industrial relays with four changeover contacts, bolt connection, for mounting on NS 35/7,5



ECOR-2-BSC3/4X21 - Relay base

2907521

<https://www.phoenixcontact.com/gb/products/2907521>

ECOR-2 relay base, for industrial relay with 2 or 4 changeover contacts, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5



REL-IR-BL/L-115AC/4X21 - Single relay

1109564

<https://www.phoenixcontact.com/gb/products/1109564>



ECOR-2-BSC2/4X21 - Relay base

1089994

<https://www.phoenixcontact.com/gb/products/1089994>



ECOR-2 relay base, for industrial relay with 2 or 4 changeover contacts, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk