

# Spring-loaded test probe

## GKS-113 214 140 R 1502 MC

Item GKS-113-1512



GO TO PRODUCT


**ingun**<sup>®</sup>

Partner for Future Technology

- Screw-in test probes for applications with possible vibrations or unwanted side and axial forces (migration of the test probe out of the receptacle is reliably prevented)
- The screw-in test probe is securely installed in the KS using a torque screwdriver and bit tool. The required screw-in torque is applied via a square post on the receptacle.
- Stainless steel versions for temperatures from -100 °C up to +200 °C available



1:1



### General data

|                                 |                                  |
|---------------------------------|----------------------------------|
| Product group:                  | Screw-in test probe              |
| Sub-product group:              | Screw-in test probe              |
| Series:                         | GKS-113 M screw-in               |
| Grid:                           | 4 mm [157 mil]                   |
| Contacting from:                | Pad, pin, posts                  |
| Magnetic:                       | Yes                              |
| Installation type:              | Screw-in                         |
| Quick-exchange system:          | Yes                              |
| Adjustable installation height: | No                               |
| Non-rotating:                   | No                               |
| Screw-in torque:                | 10 - 20 cNm [.885 - 1.77 lbf·in] |
| Compatible receptacle(s):       | KS-113 M                         |
| Min. temperature:               | - 40 °C [- 104 °F]               |
| Max. temperature:               | + 80 °C [+ 176 °F]               |
| RoHS-compliant:                 | RoHS-3;6a;6c                     |

### Electrical data

|                                        |           |
|----------------------------------------|-----------|
| Current load capacity / rated current: | 5 A       |
| Typical resistance (Ri):               | <100 mOhm |

### Mechanical data

|                                 |                   |
|---------------------------------|-------------------|
| Total length:                   | 28.3 mm [1.11 in] |
| Barrel diameter:                | 2.65 mm [.104 in] |
| Maximum stroke:                 | 5.3 mm [.208 in]  |
| Spring pre-load:                | 0.39 N [1.40 ozf] |
| Collar height:                  | 02                |
| Spring force at working stroke: | 1.5 N [5.39 ozf]  |
| Recommended working stroke:     | 4 mm [.157 in]    |

### Tip style data

|                     |                                 |
|---------------------|---------------------------------|
| Tip style:          | 14 4-point crown, self-cleaning |
| Tip diameter:       | 1.4 mm [.055 in]                |
| Tip style surface:  | R rhodium                       |
| Tip style material: | 2 steel                         |

SCREW-IN TEST PROBE

# Spring-loaded test probe


## GKS-113 214 140 R 1502 MC

Item GKS-113-1512



**ingun**<sup>®</sup>

Partner for Future Technology



### INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162  
78467, Constance, Germany  
Phone +49 7531 8105-0  
Customer hotline +49 7531 8105-888  
Fax +49 7531 8105-65  
info@ingun.com



Prices and delivery times on request.  
Technical changes reserved. 03/24\_GB

Learn more about  
Screw-in test probe



SCREW-IN TEST PROBE

ingun.com