

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PLC-INTERFACE for input functions, consisting of PLC-BPT.../SEN basic terminal block with push-in connection and plug-in miniature solid-state relay, for mounting on DIN rail NS 35/7,5, 1 N/O contact, input: 24 V DC, output: 3 - 48 V DC/100 mA

## Your advantages

- Time savings of up to 60 %
- Efficient connection to system cabling using V8 adapter
- No need for additional modular terminal blocks
- Relay modules with safe isolation according to DIN EN 50178 between coil and contact
- Space savings of up to 80 %
- Functional plug-in bridges
- Sensor connected directly to relay module

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 2900358             |
| Packing unit                         | 10 pc               |
| Minimum order quantity               | 1 pc                |
| Sales key                            | CK6235              |
| Product key                          | CK6235              |
| Catalog page                         | Page 381 (C-5-2019) |
| GTIN                                 | 4046356506847       |
| Weight per piece (including packing) | 33.73 g             |
| Weight per piece (excluding packing) | 33.57 g             |
| Customs tariff number                | 85364190            |
| Country of origin                    | DE                  |

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## Technical data

### Product properties

|                |                          |
|----------------|--------------------------|
| Product type   | Solid-state relay module |
| Product family | PLC-INTERFACE            |
| Application    | Input function           |
| Operating mode | 100% operating factor    |

### Insulation characteristics

|            |                  |
|------------|------------------|
| Insulation | Basic insulation |
|------------|------------------|

### Insulation characteristics: Standards/regulations

|                      |                  |
|----------------------|------------------|
| Insulation           | Basic insulation |
| Overvoltage category | III              |
| Pollution degree     | 2                |

### Electrical properties

|                                                 |                                      |
|-------------------------------------------------|--------------------------------------|
| Maximum power dissipation for nominal condition | 0.2 W                                |
| Test voltage (Input/output)                     | 2.5 kV (50 Hz, 1 min., input/output) |

### Input data

|                                                      |                                                        |
|------------------------------------------------------|--------------------------------------------------------|
| Nominal input voltage $U_N$                          | 24 V DC                                                |
| Input voltage range in reference to $U_N$            | 0.8 ... 1.2                                            |
| Input voltage range                                  | 19.2 V DC ... 28.8 V DC                                |
| Switching threshold "0" signal in reference to $U_N$ | $\leq 0.4$                                             |
| Switching threshold "1" signal in reference to $U_N$ | $\geq 0.8$                                             |
| Typical input current at $U_N$                       | 8.5 mA                                                 |
| Typical response time                                | 20 $\mu$ s (at $U_N$ )                                 |
| Typical turn-off time                                | 300 $\mu$ s (at $U_N$ )                                |
| Operating voltage display                            | Yellow LED                                             |
| Protective circuit                                   | Reverse polarity protection; Polarity protection diode |
|                                                      | Freewheeling diode; Freewheeling diode                 |
| Transmission frequency                               | 300 Hz                                                 |

### Output data

|                                                  |                                                        |
|--------------------------------------------------|--------------------------------------------------------|
| Contact switching type                           | 1 N/O contact                                          |
| Design of digital output                         | electronic                                             |
| Output voltage range                             | 3 V DC ... 48 V DC                                     |
| Limiting continuous current                      | 100 mA                                                 |
| Voltage drop at max. limiting continuous current | $\leq 1$ V                                             |
| Output circuit                                   | 2-conductor, floating                                  |
| Protective circuit                               | Reverse polarity protection; Polarity protection diode |
|                                                  | Surge protection                                       |

### Connection data

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

|                                  |                                      |
|----------------------------------|--------------------------------------|
| Connection method                | Push-in connection                   |
| Stripping length                 | 10 mm                                |
| Conductor cross section rigid    | 0.14 mm² ... 2.5 mm²                 |
| Conductor cross section flexible | 0.14 mm² ... 2.5 mm²                 |
|                                  | 0.2 mm² ... 2.5 mm² (Single ferrule) |
|                                  | 2x 0.5 mm² ... 1 mm² (TWIN ferrule)  |
| Conductor cross section AWG      | 26 ... 14                            |

## Dimensions

|        |        |
|--------|--------|
| Width  | 6.2 mm |
| Height | 80 mm  |
| Depth  | 94 mm  |

## Material specifications

|                                        |                 |
|----------------------------------------|-----------------|
| Color                                  | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0 (Housing)    |

## Environmental and real-life conditions

### Ambient conditions

|                                         |                  |
|-----------------------------------------|------------------|
| Ambient temperature (operation)         | -25 °C ... 60 °C |
| Ambient temperature (storage/transport) | -25 °C ... 70 °C |

## Approvals

### CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

### UKCA

|             |                |
|-------------|----------------|
| Certificate | UKCA-compliant |
|-------------|----------------|

### Shipbuilding approval

|             |            |
|-------------|------------|
| Certificate | TAE0000196 |
|-------------|------------|

### Corrosive gas test

|                |                            |
|----------------|----------------------------|
| Identification | ISA-S71.04. G3 Harsh Group |
|                | EN 60068-2-60              |

### DNV GL data

|             |                                                                                         |
|-------------|-----------------------------------------------------------------------------------------|
| Temperature | D                                                                                       |
| Humidity    | A                                                                                       |
| Vibration   | B/C                                                                                     |
| EMC         | B                                                                                       |
| Enclosure   | Required protection according to the Rules shall be provided upon installation on board |

## EMC data

|                       |                                        |
|-----------------------|----------------------------------------|
| Low Voltage Directive | Conformance with Low Voltage Directive |
|-----------------------|----------------------------------------|

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358  
<https://www.phoenixcontact.com/gb/products/2900358>

|                               |                                |
|-------------------------------|--------------------------------|
| Electromagnetic compatibility | Conformance with EMC directive |
|-------------------------------|--------------------------------|

## Standards and regulations

|                       |               |
|-----------------------|---------------|
| Standards/regulations |               |
| Standards/regulations | IEC 60947-5-1 |

## Mounting


|                       |                           |
|-----------------------|---------------------------|
| Mounting type         | DIN rail mounting         |
| Assembly instructions | in rows with zero spacing |
| Mounting position     | any                       |

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module

2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## Drawings



# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358  
<https://www.phoenixcontact.com/gb/products/2900358>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2900358>



**cUL Recognized**  
Approval ID: FILE E 238705



**UL Recognized**  
Approval ID: FILE E 238705



**EAC**  
Approval ID: TR\_TS\_D\_00573\_c



**DNV GL**  
Approval ID: TAE0000196



**UL Listed**  
Approval ID: FILE E 172140



**cUL Listed**  
Approval ID: FILE E 172140



**cULus Listed**  
Approval ID: E140324

**cULus Recognized**

**cULus Listed**

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27371604 |
| ECLASS-12.0 | 27371604 |
| ECLASS-13.0 | 27371604 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001504 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358  
<https://www.phoenixcontact.com/gb/products/2900358>

## Environmental product compliance

|            |                                                                                                              |
|------------|--------------------------------------------------------------------------------------------------------------|
| REACH SVHC | Lead 7439-92-1                                                                                               |
|            | Hexahydromethylphthalic anhydride                                                                            |
| China RoHS | Environmentally Friendly Use Period = 50 years                                                               |
|            | For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads" |

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## Accessories

**i** Note: Applying some accessories below might limit this product.

### FBST 500-PLC RD - Continuous plug-in bridge

2966786

<https://www.phoenixcontact.com/gb/products/2966786>



Continuous plug-in bridge, length: 500 mm, color: red

**i** Max. current carrying capacity: 32 A

---

### FBST 500-PLC BU - Continuous plug-in bridge

2966692

<https://www.phoenixcontact.com/gb/products/2966692>



Continuous plug-in bridge, length: 500 mm, color: blue

**i** Max. current carrying capacity: 32 A

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## FBST 500-PLC GY - Continuous plug-in bridge

2966838

<https://www.phoenixcontact.com/gb/products/2966838>



Continuous plug-in bridge, length: 500 mm, color: gray

 Max. current carrying capacity: 32 A

---

## FBST 6-PLC RD - Single plug-in bridge

2966236

<https://www.phoenixcontact.com/gb/products/2966236>



Single plug-in bridge, number of positions: 2, length: 6 mm, color: red

 Max. current carrying capacity: 6 A

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358


<https://www.phoenixcontact.com/gb/products/2900358>

## FBST 6-PLC BU - Single plug-in bridge

2966812

<https://www.phoenixcontact.com/gb/products/2966812>

Single plug-in bridge, number of positions: 2, length: 6 mm, color: blue



 Max. current carrying capacity: 6 A


---

## FBST 6-PLC GY - Single plug-in bridge

2966825

<https://www.phoenixcontact.com/gb/products/2966825>

Single plug-in bridge, number of positions: 2, length: 6 mm, color: gray



 Max. current carrying capacity: 6 A

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## FBST 8-PLC GY - Single plug-in bridge

2967688

<https://www.phoenixcontact.com/gb/products/2967688>

Single plug-in bridge, number of positions: 2, length: 8 mm, color: gray




 Max. current carrying capacity: 6 A

---

## PLC-V8/FLK14/IN - System connection

2296553

<https://www.phoenixcontact.com/gb/products/2296553>



V8 adapter for 8 x PLC-INTERFACE (6.2 mm), controller: PLC system cabling of input cards, connection 1: IDC/FLK pin strip 1x 14-position, connection 2: Plug-in connection (Can be snapped onto 8x PLC-INTERFACE terminals), connection 3: Screw connection 1x 2-position, number of channels: 8, control logic: plusschaltend

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## PLC-V8/FLK14/IN/M - System connection

2304115

<https://www.phoenixcontact.com/gb/products/2304115>



V8 adapter for 8 x PLC-INTERFACE (6.2 mm), controller: PLC system cabling of input cards, connection 1: IDC/FLK pin strip 1x 14-position, connection 2: Plug-in connection (Can be snapped onto 8x PLC-INTERFACE terminals), connection 3: Screw connection 1x 2-position, number of channels: 8, control logic: minusschaltend

---

## PLC-V8/D15S/IN - System connection

2296074

<https://www.phoenixcontact.com/gb/products/2296074>



V8 adapter for 8 x PLC-INTERFACE (6.2 mm), controller: PLC system cabling of input cards, connection 1: D-SUB pin strip 1x 15-position, connection 2: Plug-in connection (Can be snapped onto 8x PLC-INTERFACE terminals), connection 3: Screw connection 1x 2-position, number of channels: 8, control logic: plusschaltend

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## PLC-V8/D15B/IN - System connection

2296087

<https://www.phoenixcontact.com/gb/products/2296087>



V8 adapter for 8 x PLC-INTERFACE (6.2 mm), controller: PLC system cabling of input cards, connection 1: D-SUB socket strip 1x 15-position, connection 2: Plug-in connection (Can be snapped onto 8x PLC-INTERFACE terminals), connection 3: Screw connection 1x 2-position, number of channels: 8, control logic: plusschaltend

---

## ZB 6:UNBEDRUCKT - Zack marker strip

1051003

<https://www.phoenixcontact.com/gb/products/1051003>



Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## ZB 6 CUS - Zack marker strip

0824992

<https://www.phoenixcontact.com/gb/products/0824992>



Zack marker strip, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

---

## ZB 6,LGS:FORTL.ZAHLEN - Zack marker strip

1051016

<https://www.phoenixcontact.com/gb/products/1051016>



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 491 ... 500, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## ZB 6,QR:FORTL.ZAHLEN - Zack marker strip

1051029

<https://www.phoenixcontact.com/gb/products/1051029>



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, Printed vertically: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 491 ... 500, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

---

## ZB 6,LGS:GLEICHE ZAHLEN - Zack marker strip

1051032

<https://www.phoenixcontact.com/gb/products/1051032>



Zack marker strip, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, printed horizontally: Identical numbers 1 or 2, etc. up to 100, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## ZB 6,LGS:L1-N,PE - Marker for terminal blocks

1051414

<https://www.phoenixcontact.com/gb/products/1051414>



Marker for terminal blocks, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, horizontal: L1, L2, L3, N, PE, L1, L2, L3, N, PE, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

---

## ZB 6,LGS:U-N - Marker for terminal blocks

1051430

<https://www.phoenixcontact.com/gb/products/1051430>



Marker for terminal blocks, Strip, white, labeled, can be labeled with: CMS-P1-PLOTTER, printed horizontally: U, V, W, N, GND, U, V, W, N, GND, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 6.15 x 10.5 mm, Number of individual labels: 10

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## UC-TM 6 - Marker for terminal blocks

0818085

<https://www.phoenixcontact.com/gb/products/0818085>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 80

---

## UC-TM 6 CUS - Marker for terminal blocks

0824589

<https://www.phoenixcontact.com/gb/products/0824589>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 80

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## UCT-TM 6 - Marker for terminal blocks

0828736

<https://www.phoenixcontact.com/gb/products/0828736>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 60

## UCT-TM 6 CUS - Marker for terminal blocks

0829602

<https://www.phoenixcontact.com/gb/products/0829602>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 6.2 mm, lettering field size: 5.6 x 10.5 mm, Number of individual labels: 60

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## NS 35/ 7,5 PERF 2000MM - DIN rail perforated

0801733

<https://www.phoenixcontact.com/gb/products/0801733>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

---

## NS 35/ 7,5 UNPERF 2000MM - DIN rail, unperforated

0801681

<https://www.phoenixcontact.com/gb/products/0801681>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## NS 35/ 7,5 WH PERF 2000MM - DIN rail perforated

1204119

<https://www.phoenixcontact.com/gb/products/1204119>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

---

## NS 35/ 7,5 WH UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1204122

<https://www.phoenixcontact.com/gb/products/1204122>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## NS 35/ 7,5 AL UNPERF 2000MM - DIN rail, unperforated

0801704

<https://www.phoenixcontact.com/gb/products/0801704>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver

---

## NS 35/ 7,5 ZN PERF 2000MM - DIN rail perforated

1206421

<https://www.phoenixcontact.com/gb/products/1206421>



DIN rail perforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

NS 35/ 7,5 ZN UNPERF 2000MM - DIN rail, unperforated

1206434

<https://www.phoenixcontact.com/gb/products/1206434>



DIN rail, unperforated, Pack of 25 (50 m), acc. to EN 60715, material: Steel, galvanized, Standard profile, color: silver

---

NS 35/ 7,5 CU UNPERF 2000MM-VPE 10 - DIN rail, unperforated

0801762

<https://www.phoenixcontact.com/gb/products/0801762>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## NS 35/ 7,5 CAP - End cap

1206560

<https://www.phoenixcontact.com/gb/products/1206560>

DIN rail end piece, for DIN rail NS 35/7.5



---

## NS 35/15 PERF 2000MM - DIN rail perforated

1201730

<https://www.phoenixcontact.com/gb/products/1201730>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## NS 35/15 UNPERF 2000MM - DIN rail, unperforated

1201714

<https://www.phoenixcontact.com/gb/products/1201714>



DIN rail, unperforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile, color: silver

---

## NS 35/15 WH PERF 2000MM - DIN rail perforated

0806602

<https://www.phoenixcontact.com/gb/products/0806602>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: white

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## NS 35/15 WH UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1204135

<https://www.phoenixcontact.com/gb/products/1204135>



DIN rail, unperforated, Pack of 10 (20 m), similar to EN 60715, material: Steel, Galvanized, white passivated, Standard profile, color: silver

---

## NS 35/15 AL UNPERF 2000MM - DIN rail, unperforated

1201756

<https://www.phoenixcontact.com/gb/products/1201756>



DIN rail, unperforated, similar to EN 60715, material: Aluminum, uncoated, Standard profile, color: silver

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## NS 35/15 ZN PERF 2000MM - DIN rail perforated

1206599

<https://www.phoenixcontact.com/gb/products/1206599>



DIN rail perforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, Standard profile, color: silver

---

## NS 35/15 ZN UNPERF 2000MM - DIN rail, unperforated

1206586

<https://www.phoenixcontact.com/gb/products/1206586>



DIN rail, unperforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, Standard profile, color: silver

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## NS 35/15 CU UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1201895

<https://www.phoenixcontact.com/gb/products/1201895>



DIN rail, unperforated, Pack of 10 (20 m), similar to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

---

## NS 35/15 CAP - End cap

1206573

<https://www.phoenixcontact.com/gb/products/1206573>



DIN rail end piece, for DIN rail NS 35/15

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## NS 35/15-2,3 UNPERF 2000MM-VPE 10 - DIN rail, unperforated

1201798

<https://www.phoenixcontact.com/gb/products/1201798>



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Steel, galvanized, passivated with a thick layer, Standard profile 2.3 mm, color: silver

---

## PLC-ATP BK - Separating plate

2966841

<https://www.phoenixcontact.com/gb/products/2966841>



Separating plate, 2 mm thick, required at the start and end of a PLC terminal strip. Furthermore, it is used for: visual separation of groups, safe isolation of different voltages of neighboring PLC relays in acc. with DIN VDE 0106-101, isolation

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module



2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## PLC-ESK GY - Power terminal block

2966508

<https://www.phoenixcontact.com/gb/products/2966508>



Power terminal block, for the input of up to four potentials, for mounting on NS 35/7.5

---

## SZF 1-0,6X3,5 - Screwdriver

1204517

<https://www.phoenixcontact.com/gb/products/1204517>



Actuation tool, for ST terminal blocks, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip

# PLC-OPT- 24DC/ 48DC/100/SEN - Solid-state relay module




2900358

<https://www.phoenixcontact.com/gb/products/2900358>

## OPT-24DC/ 48DC/100 - Miniature solid-state relay

2966618

<https://www.phoenixcontact.com/gb/products/2966618>



Plug-in miniature solid-state relay, input solid-state relay, 1 N/O contact, input: 24 V DC, output: 3 - 48 V DC/100 mA

---

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)