

High-current clamp, round contact

HKR-694 400 080 S 10002

Item HKR-694-0001





GO TO PRODUCT

ingun[®]

Partner for Future Technology

UTILITY
MODEL

PATENT
PENDING



HIGH-CURRENT TEST PROBE

High-current clamp, round contact

HKR-694 400 080 S 10002

Item HKR-694-0001



GO TO PRODUCT

ingun[®]

Partner for Future Technology

General data

Product group:	High-current test probe
Sub-product group:	High-current clamps (flat/round)
Series:	HKR-694
Grid:	6.4 mm [251 mil]
Contacting from:	Post
Magnetic:	Yes
Installation type:	Bayonet
Quick-exchange system:	Yes
Adjustable installation height:	No
Non-rotating:	Yes
Compatible receptacle(s):	KS-617
Min. temperature:	- 100 °C [- 212 °F]
Max. temperature:	+ 150 °C [+ 302 °F]
RoHS-compliant:	RoHS-3;6c

Electrical data


Current load capacity / rated current:	15 A
Typical resistance (Ri):	<10 mOhm

Mechanical data

Total length:	56.2 mm [2.21 in]
Barrel diameter:	3.5 mm [.137 in]
Maximum stroke:	5.5 mm [.216 in]
Spring pre-load:	6.11 N [21.9 ozf]
Collar height:	02
Spring force at working stroke:	10 N [35.9 ozf]
Recommended working stroke:	4.4 mm [.173 in]

Tip style data

Tip style:	00 flat with bore
Tip diameter:	6.8 mm [.267 in]
Tip style surface:	S silver
Tip style material:	6 bronze



INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 04/24_GB

Learn more about
High-current test probe



HIGH-CURRENT TEST PROBE

ingun.com