

# Switching probe

## SKS-465 302 590 A 2002 SF

Item SKS-465-0179



GO TO PRODUCT


**ingun**<sup>®</sup>

Partner for Future Technology

- For a wide range of applications: performs components detection check, is a switch for detecting closed/open states, and a signal transmitter for process control
- Various collar heights are available on the receptacles to adjust the installation height
- The installation height can be varied, and the position of the switching point can be precisely adjusted via the probe's thread. The SKS is secured in the correct position by crimp point in the KS.
- The electrical connection is ensured by installation using a receptacle, optionally available with a quick-change system for easy exchange during maintenance



1:1



### General data

|                                 |                                                  |
|---------------------------------|--------------------------------------------------|
| Product group:                  | Switching probes                                 |
| Sub-product group:              | SKS (screwed-in)                                 |
| Series:                         | SKS-465 SF quick-exchange/ plug system, screw-in |
| Grid:                           | 6.5 mm [255 mil]                                 |
| Contacting from:                | Pin, posts, bead, flat contact                   |
| Magnetic:                       | Yes                                              |
| Installation type:              | Screw-in                                         |
| Quick-exchange system:          | Yes                                              |
| Type of test probe connection:  | Plug                                             |
| Adjustable installation height: | Yes                                              |
| Non-rotating:                   | No                                               |
| Screw-in torque:                | 3 - 5 cNm [.265 - .442 lbf-in]                   |
| Compatible connector(s):        | SE-215                                           |
| Compatible receptacle(s):       | KS-465 M, KS-465 M-F                             |
| Min. temperature:               | - 40 °C [- 104 °F]                               |
| Max. temperature:               | + 80 °C [+ 176 °F]                               |
| RoHS-compliant:                 | RoHS-3;6c                                        |

### Electrical data

|                                        |     |
|----------------------------------------|-----|
| Current load capacity / rated current: | 3 A |
|----------------------------------------|-----|

### Mechanical data

|                                  |                   |
|----------------------------------|-------------------|
| Total length:                    | 44.8 mm [1.76 in] |
| Barrel diameter:                 | 2.65 mm [.104 in] |
| Maximum stroke:                  | 4.5 mm [.177 in]  |
| Spring pre-load:                 | 0.5 N [1.79 ozf]  |
| Collar height:                   | 02                |
| Switch path:                     | 1.7 mm [.066 in]  |
| Switching point:                 | 8.5 mm [.334 in]  |
| Spring force at switching point: | 0.7 N [2.51 ozf]  |

### Tip style data

|                     |                  |
|---------------------|------------------|
| Tip style:          | 02 flat          |
| Tip diameter:       | 5.9 mm [.232 in] |
| Tip style surface:  | A gold           |
| Tip style material: | 3 CuBe           |

### INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162  
78467, Constance, Germany  
Phone +49 7531 8105-0  
Customer hotline +49 7531 8105-888  
Fax +49 7531 8105-65  
info@ingun.com



Prices and delivery times on request.  
Technical changes reserved. 04/24\_GB

Learn more about  
Test probes



ingun.com