





The first Ultra-functional Double HD LCD Screens charger with 8A (total current) speedy charge!
Double USB output ports! Hardware and software double protection!

Compatible With Li-ion
3.6V/3.7V batteries:
NiMH/NiCd 1.2V batteries:
A/AA/AAA/C

10440	18500
14500	18650
16340	20700
17340	21700
18350	26500
18490	26650

AC input power	AC100V-240V 50/60Hz
DC input power	DC 12V 4A
Double USB output power	USB 5V 1A
USB output floating current	<5mA
8*0.25A CC current	250mA±10%
8*0.5A CC current	500mA±10%
8*1.0A CC current	1000mA±10%
4*2.0A CC current	2000mA±10%
Auto cut-off voltage	4.20V±0.05V
CV cut-off current	<10%max
Standby current	<100Ma
Activation current	<100Ma
Auto recharge voltage	4.10V±0.1V
Operation temperature	-0°C-40°C
Storage temperature	-40°C-+70°C








Error Reporting Protection

When the battery is connected reversely or there is a short circuit in the charger, the main display screen will light up and point out the wrong slot by flashing "ERROR".

Hardware And Software Double Protection

The main display screen will be off automatically if there is no activity after 30 seconds



6 Protection Levels For Every EFEST Charger

1. 0V activation recovery function
2. Reverse polarity protection
3. Short circuit protection
4. Automatic over charging/discharging protection
5. Hardware and software double protection
6. Error reporting protection

PACKAGE

1*7 Languages Package Box
1*7 Languages Operation Manual
1*Warranty Card
1*LUC V8 Charger
1*DC 12V 4A Adapter

WARNING

