


CATALOG CARD

Quick connector 2,5mm², 4 pins, PC254CL



Information	
Index	E.4182
EAN	5905793080657
Certificates and standards	
CE, PN-EN IEC 60947-1:2021-07	
Link to the declaration	
https://www.pawbol.pl/wp-content/uploads/2023/07/E.14J-Zlaczki-samozaciskowe-bezgwintowe-przezroczyste-szybkoszlaczki.pdf	
Technical data	
Colour	Red (transparent housing)
Electrical data and parameters	
Rated insulation voltage	450V
Rated current	24A
Number of contacts	4
Working temperature	From -40°C to 85°C
Dimensions	
Height	18mm
Width	6mm
Length	16,2mm
Weight	1,5g
Installation information	
Cable stripping length	11mm
Connection type	Quick connector
Conductor cross-sections for wire	0,5mm ² - 2,5mm ²
Conductor cross-sections for tinned cable	0,5mm ² - 2,5mm ²
Conductor cross-sections for a cable fertilized with a ferrule	0,5mm ² - 1,5mm ²
Packing	
Number of pieces in the package	100

PAWBOL S.A. MANUFACTURER OF ELECTROTECHNICAL EQUIPMENT