

IB IL 24 DO 4-PAC - Digital module

2861276

<https://www.phoenixcontact.com/gb/products/2861276>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Inline, Digital output terminal, Digital outputs: 4, 24 V DC, 500 mA, connection technology: 3-conductor, transmission speed in the local bus: 500 kbps, degree of protection: IP20, including Inline connector and labeling field

Product description

The terminal is designed for use within an Inline station. It is used to output digital signals.

Your advantages

- 4 digital outputs
- Connection of actuators in 2- and 3-conductor technology
- Nominal current per output: 500 mA
- Total current of the terminal: 2 A
- Short-circuit and overload-protected outputs

Commercial data

Item number	2861276
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DRI132
Product key	DRI132
Catalog page	Page 128 (C-6-2019)
GTIN	4017918894214
Weight per piece (including packing)	94.6 g
Weight per piece (excluding packing)	66 g
Customs tariff number	85389099
Country of origin	DE

IB IL 24 DO 4-PAC - Digital module


2861276

<https://www.phoenixcontact.com/gb/products/2861276>



Technical data

Dimensions

Dimensional drawing	
	
Width	12.2 mm
Height	140.5 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

Notes

Utilization restriction	
CCCex note	Use in potentially explosive areas is not permitted in China.

Interfaces

Inline local bus	
Number of interfaces	2
Connection method	Inline data jumper
Transmission speed	500 kbps

System properties

Module	
ID code (dec.)	189
ID code (hex)	BD
Length code (hex)	41
Length code (dec)	65
Process data channel	4 bit
Input address area	0 bit
Output address area	4 bit
Register length	4 bit
Required parameter data	3 Byte
Required configuration data	4 Byte

Output data

Digital:	
Output name	Digital outputs
Connection method	Spring-cage connection

IB IL 24 DO 4-PAC - Digital module



2861276

<https://www.phoenixcontact.com/gb/products/2861276>

Connection technology	3-conductor
Number of outputs	4
Protective circuit	Overload protection, short-circuit protection; electronic
Output voltage	24 V DC ($U_S - 1\text{ V}$)
Limitation of the voltage induced on circuit interruption	-46 V ... -15 V
Maximum inrush current	max. 1.5 A (for 20 ms)
Output current	max. 500 mA (per channel) max. 2 A (Device)
Nominal output voltage	24 V DC
Output voltage when switched off	max. 2 V
Output current when switched off	max. 300 μA
Nominal load, inductive	12 VA (1.2 H, 50 Ω)
Nominal load, lamp	12 W
Nominal load, ohmic	12 W (48 Ω)
Maximum operating frequency with ohmic nominal load	max. 300 Hz (this switching frequency is limited by the data rate selected, the number of bus devices, the structure of the bus, the software used and the control or computer system used)
Reverse voltage resistance to short pulses	Reverse voltage proof
Behavior with overload	Auto restart
Behavior with inductive overload	Output can be destroyed
Behavior at voltage switch-off	The output follows the power supply without delay
Overcurrent shut-down	min. 0.7 A
Output current with ground connection interrupt when switched off	max. 25 mA

Product properties

Product type	I/O component
Product family	Inline
Type	modular
Scope of delivery	including Inline connector and labeling field
No. of channels	4
Operating mode	Process data operation with 4 bits
Diagnostics messages	Short-circuit or overload of the digital outputs Error message in the diagnostic code (bus) and display (2 Hz) via the LED (D) on the module

Insulation characteristics

Overvoltage category	II (IEC 60664-1, EN 60664-1)
Pollution degree	2 (IEC 60664-1, EN 60664-1)

Electrical properties

Maximum power dissipation for nominal condition	48 W
---	------

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (via voltage jumper)
Current draw	max. 44 mA

IB IL 24 DO 4-PAC - Digital module



2861276

<https://www.phoenixcontact.com/gb/products/2861276>

Power consumption	max. 0.33 W
Potentials: Segment circuit supply (U_S)	
Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 2 A
Electrical isolation/isolation of the voltage ranges	
Test voltage: 7.5 V supply (bus logics)/24 V supply (I/O)	500 V AC, 50 Hz, 1 min.
Test voltage: 24 V supply (I/O) / functional ground	500 V AC, 50 Hz, 1 min.
Test voltage: 7.5 V supply (bus logic)/functional ground	500 V AC, 50 Hz, 1 min.

Connection data

Connection technology

Connection name	Inline connector
-----------------	------------------

Conductor connection

Connection method	Spring-cage connection
Conductor cross section rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross section flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross section AWG	28 ... 16
Stripping length	8 mm

Inline connector

Connection method	Spring-cage connection
Conductor cross section, rigid	0.08 mm ² ... 1.5 mm ²
Conductor cross section, flexible	0.08 mm ² ... 1.5 mm ²
Conductor cross section AWG	28 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)

Standards and regulations


Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Drawings

Block diagram




Internal wiring of the terminal points

IB IL 24 DO 4-PAC - Digital module


2861276

<https://www.phoenixcontact.com/gb/products/2861276>

Dimensional drawing



Connection diagram



IB IL 24 DO 4-PAC - Digital module



2861276

<https://www.phoenixcontact.com/gb/products/2861276>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2861276>

	UL Recognized Approval ID: FILE E 140324
	EAC Approval ID: TR TS_D_01921-19
	DNV GL Approval ID: TAA00000BN
	BV Approval ID: 20977/C0 BV
	BSH Approval ID: 658a
	RINA Approval ID: ELE121121XG
	ABS Approval ID: 22-2226444-PDA
	UAE-RoHS Approval ID: 22-04-13090
	cUL Listed Approval ID: FILE E 199827
	UL Listed Approval ID: FILE E 199827
	cULus Listed

IB IL 24 DO 4-PAC - Digital module



2861276

<https://www.phoenixcontact.com/gb/products/2861276>

Classifications

ECLASS

ECLASS-11.0	27242604
ECLASS-12.0	27242604
ECLASS-13.0	27242604

ETIM

ETIM 9.0	EC001599
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

IB IL 24 DO 4-PAC - Digital module



2861276
<https://www.phoenixcontact.com/gb/products/2861276>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	3fd35456-0b80-4f99-8a74-5b6bc591ce0c

IB IL 24 DO 4-PAC - Digital module

2861276

<https://www.phoenixcontact.com/gb/products/2861276>



Accessories

IB IL SCN-12-OCP - Inline connector

2727624

<https://www.phoenixcontact.com/gb/products/2727624>



Connector, colored identification, for digital 4, or 16-channel Inline output terminal blocks

IB IL SCN-12 - Inline connector

2726340

<https://www.phoenixcontact.com/gb/products/2726340>



Connector, for digital 4 or 16-channel Inline terminals

IB IL 24 DO 4-PAC - Digital module

2861276

<https://www.phoenixcontact.com/gb/products/2861276>



IB IL FIELD 2 - Marking field

2727501

<https://www.phoenixcontact.com/gb/products/2727501>

Marking field, width: 12.2 mm



ESL 62X10 - Insert strip

0809492

<https://www.phoenixcontact.com/gb/products/0809492>

Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, CMS-P1-PLOTTER, mounting type: insert, lettering field size: 62 x 10 mm, Number of individual labels: 72



Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk