


REL-MR-BL- 24AC/21HC - Single relay



1109540

<https://www.phoenixcontact.com/gb/products/1109540>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pluggable miniature power relay in basic design, with power contact for high continuous currents, 1 changeover contact, input voltage 24 V AC

Commercial data

Item number	1109540
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	CKF931
Product key	CKF931
GTIN	4063151018672
Weight per piece (including packing)	14.55 g
Weight per piece (excluding packing)	289 g
Customs tariff number	85364190
Country of origin	AT

REL-MR-BL- 24AC/21HC - Single relay



1109540

<https://www.phoenixcontact.com/gb/products/1109540>

Technical data

Product properties

Product type	Single relay
Operating mode	100% operating factor
Mechanical service life	1x 10 ⁷ cycles

Insulation characteristics

Insulation	Basic insulation
------------	------------------

Insulation characteristics

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	3

Electrical properties

Service life electrical	see diagram
Maximum power dissipation for nominal condition	0.4 W
Rated insulation voltage	250 V AC
Rated surge voltage	4 kV

Input data

Coil side

Nominal input voltage U _N	24 V AC
Input voltage range	19.2 V AC ... 34.8 V AC
Mains frequency	50/60 Hz
Drive and function	monostable
Drive (polarity)	non-polarized
Typical input current at U _N	31.6 mA
Typical response time	3 ms ... 12 ms (depending on phase relation)
Typical release time range	2 ms ... 9 ms (depending on phase relation)
Coil voltage	24 V AC
Coil resistance	350 Ω ±10 %

Output data

Switching

Contact switching type	1 changeover contact
Type of switch contact	Single contact
Contact material	AgNi
Maximum switching voltage	250 V AC/DC
Minimum switching voltage	5 V (At 24 mA)
Limiting continuous current	16 A
Maximum inrush current	30 A (300 ms)

REL-MR-BL- 24AC/21HC - Single relay



1109540

<https://www.phoenixcontact.com/gb/products/1109540>

Min. switching current	10 mA (at 12 V)
Interrupting rating (ohmic load) max.	384 W (at 24 V DC)
	58 W (at 48 V DC)
	48 W (at 60 V DC)
	50 W (at 110 V DC)
	80 W (at 220 V DC)
Switching capacity	4000 VA (for 250 V AC)
	2 A (at 24 V, DC13)
	1.5 A (at 230 V, AC15)

Connection data

Connection method	Plug / solder connection
-------------------	--------------------------

Dimensions

Dimensional drawing	
Width	12.7 mm
Height	29 mm
Depth	15.7 mm

Material specifications

Color	orange (RAL 2003)
-------	-------------------

Environmental and real-life conditions

Ambient conditions	
Degree of protection	RT II
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Standards and regulations


Standards/regulations	IEC 60664
	EN 61810-1

Mounting


Mounting type	Plug-in mounting
Mounting position	any


Drawings

Circuit diagram



Diagram





Permissible humidity for operation and storage.


The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures $\leq 0^\circ\text{C}$ must be prevented


Area B: Condensation at ambient temperatures $> 0^\circ\text{C}$ must be prevented

On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature $\leq 25^\circ\text{C}$.

Drilling plan/solder pad geometry




Basic pitch 2.5 mm




- ① 250 V AC, ohmic load (DC coils)
- ② 250 V AC, ohmic load (AC coils)

Electrical service life



Diagram



- ① DC coils
- ② AC coils

Operating voltage range

REL-MR-BL- 24AC/21HC - Single relay



1109540

<https://www.phoenixcontact.com/gb/products/1109540>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1109540>



cUL Recognized
Approval ID: FILE E 228652



UL Recognized
Approval ID: FILE E 228652

cULus Recognized

REL-MR-BL- 24AC/21HC - Single relay



1109540

<https://www.phoenixcontact.com/gb/products/1109540>

Classifications

ECLASS

ECLASS-11.0	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601

ETIM

ETIM 8.0	EC001437
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

REL-MR-BL- 24AC/21HC - Single relay



1109540

<https://www.phoenixcontact.com/gb/products/1109540>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

REL-MR-BL- 24AC/21HC - Single relay



1109540

<https://www.phoenixcontact.com/gb/products/1109540>

Mandatory accessories

ECOR-1-BSC2-RT/2X21 - Relay base

1027546

<https://www.phoenixcontact.com/gb/products/1027546>

ECOR-1... relay base, for miniature power relays or miniature switching relays with 1 or 2 changeover contacts, bolt connection, for mounting on NS 35/7,5.



ECOR-1-BSC3/2X21 - Relay base

2907518

<https://www.phoenixcontact.com/gb/products/2907518>

ECOR-1... relay base, for miniature power relay or miniature switching relay with 1 or 2 changeover contacts, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5



Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

info@phoenixcontact.co.uk