

# REL-IR4/LDP- 12DC/4X21 - Single relay



2903676  
<https://www.phoenixcontact.com/gb/products/2903676>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in industrial relay with power contacts and additional hard gold plating, 4 changeover contacts, test button, status LED, freewheeling diode, mechanical switching position indicator, polarity: A1+, A2-, coil voltage: 12 V DC

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 2903676             |
| Packing unit                         | 10 pc               |
| Minimum order quantity               | 10 pc               |
| Sales key                            | CK6193              |
| Product key                          | CK6193              |
| Catalog page                         | Page 300 (C-5-2019) |
| GTIN                                 | 4046356758895       |
| Weight per piece (including packing) | 35.08 g             |
| Weight per piece (excluding packing) | 34.03 g             |
| Customs tariff number                | 85364190            |
| Country of origin                    | PL                  |

# REL-IR4/LDP- 12DC/4X21 - Single relay



2903676

<https://www.phoenixcontact.com/gb/products/2903676>

## Technical data

### Product properties

|                         |                                |
|-------------------------|--------------------------------|
| Product type            | Single relay                   |
| Operating mode          | 100% operating factor          |
| Mechanical service life | approx. $2 \times 10^7$ cycles |

### Insulation characteristics

|            |                  |
|------------|------------------|
| Insulation | Basic insulation |
|------------|------------------|

### Insulation characteristics

|                      |                  |
|----------------------|------------------|
| Insulation           | Basic insulation |
| Overvoltage category | II               |
| Pollution degree     | 2                |

### Electrical properties

|                                                      |                                                                            |
|------------------------------------------------------|----------------------------------------------------------------------------|
| Service life electrical                              | see diagram                                                                |
| Maximum power dissipation for nominal condition      | 0.94 W                                                                     |
| Test voltage (Winding/contact)                       | 2.5 kV <sub>rms</sub> (50 Hz, 1 min., winding/contact)                     |
| Test voltage (Changeover contact/changeover contact) | 2 kV <sub>rms</sub> (50 Hz, 1 min., changeover contact/changeover contact) |
| Rated insulation voltage                             | 250 V AC                                                                   |
| Rated surge voltage                                  | 2.5 kV                                                                     |

### Input data

#### Coil side

|                                |                                |
|--------------------------------|--------------------------------|
| Nominal input voltage $U_N$    | 12 V DC                        |
| Input voltage range            | 9.6 V DC ... 21.6 V DC (20 °C) |
| Drive and function             | monostable                     |
| Drive (polarity)               | polarized                      |
| Typical input current at $U_N$ | 78 mA                          |
| Typical response time          | 13 ms                          |
| Typical release time           | 14 ms                          |
| Protective circuit             | Freewheeling diode             |
| Status display                 | Yellow LED                     |

### Output data

#### Switching

|                             |                       |
|-----------------------------|-----------------------|
| Contact switching type      | 4 changeover contacts |
| Type of switch contact      | Single contact        |
| Contact material            | AgNi                  |
| Maximum switching voltage   | 250 V AC/DC           |
| Minimum switching voltage   | 5 V (At 24 mA)        |
| Limiting continuous current | 6 A                   |

# REL-IR4/LDP- 12DC/4X21 - Single relay



2903676

<https://www.phoenixcontact.com/gb/products/2903676>

|                                       |                            |
|---------------------------------------|----------------------------|
| Maximum inrush current                | 16 A (20 ms, N/O contacts) |
| Min. switching current                | 5 mA (at 24 V)             |
| Interrupting rating (ohmic load) max. | 144 W (at 24 V DC)         |
|                                       | 124 W (at 48 V DC)         |
|                                       | 108 W (at 60 V DC)         |
|                                       | 52 W (at 110 V DC)         |
|                                       | 48 W (at 220 V DC)         |
|                                       | 1500 VA (for 250 V AC)     |
| Switching capacity min.               | 0.12 W                     |
| Switching capacity                    | 2 A (at 24 V, DC13)        |
|                                       | 0.22 A (at 120 V, DC13)    |
|                                       | 0.11 A (at 250 V, DC13)    |
|                                       | 1.5 A (at 24 V, AC15)      |
|                                       | 1.5 A (at 120 V, AC15)     |
|                                       | 1 A (at 240 V, AC15)       |
| Motor load according to UL 508        | 1/3 HP, 240 V AC           |

## Connection data

|                   |                    |
|-------------------|--------------------|
| Connection method | Plug-in connection |
|-------------------|--------------------|

## Dimensions

|        |         |
|--------|---------|
| Width  | 21.2 mm |
| Height | 27.5 mm |
| Depth  | 35.6 mm |

## Environmental and real-life conditions

### Ambient conditions

|                                         |                  |
|-----------------------------------------|------------------|
| Degree of protection                    | RT I             |
| Ambient temperature (operation)         | -40 °C ... 70 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

## Approvals

### Corrosive gas test

|                |                            |
|----------------|----------------------------|
| Identification | ISA-S71.04. G3 Harsh Group |
|                | EN 60068-2-60              |


## Standards and regulations

|                       |           |
|-----------------------|-----------|
| Standards/regulations | IEC 60664 |
|                       | IEC 61810 |

## Mounting


|                   |     |
|-------------------|-----|
| Mounting position | any |
|-------------------|-----|

## Drawings



Interrupting rating

Diagram



Permissible humidity for operation and storage.


The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures  $\leq 0^\circ\text{C}$  must be prevented

Area B: Condensation at ambient temperatures  $> 0^\circ\text{C}$  must be prevented

On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature  $\leq 25^\circ\text{C}$ .


Circuit diagram



Diagram




Service life reduction factor



Operating voltage range

Diagram



① 250 V AC, Ohmic load

Electrical service life

# REL-IR4/LDP- 12DC/4X21 - Single relay



2903676

<https://www.phoenixcontact.com/gb/products/2903676>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2903676>



**CSA**

Approval ID: 256725



**cUL Recognized**

Approval ID: FILE E 172140



**UL Recognized**

Approval ID: FILE E 172140



**EAC**

Approval ID: TR\_TS\_D\_00573\_c



**VDE Zeichengenehmigung**

Approval ID: 40040427

**cULus Recognized**

# REL-IR4/LDP- 12DC/4X21 - Single relay



2903676

<https://www.phoenixcontact.com/gb/products/2903676>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27371601 |
| ECLASS-12.0 | 27371601 |
| ECLASS-13.0 | 27371601 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001437 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

# REL-IR4/LDP- 12DC/4X21 - Single relay



2903676

<https://www.phoenixcontact.com/gb/products/2903676>

## Environmental product compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

# REL-IR4/LDP- 12DC/4X21 - Single relay



2903676

<https://www.phoenixcontact.com/gb/products/2903676>

## Mandatory accessories

### RIF-2-BPT/4X21 - Relay base

2900934

<https://www.phoenixcontact.com/gb/products/2900934>




Relay base RIF-2..., for industrial relay with 2 or 4 changeover contacts, Push-in connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

---

### RIF-2-BSC/4X21 - Relay base

2900932

<https://www.phoenixcontact.com/gb/products/2900932>



RIF-2... relay base, for industrial relay with 2 or 4 changeover contacts, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

---

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd

Halesfield 13, Telford

Shropshire, TF7 4PG

01952 681700

[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)