


# REL-MR-BL- 24DC/21HC - Single relay



2906285

<https://www.phoenixcontact.com/gb/products/2906285>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug-in miniature power relay in basic design, with power contact for high continuous currents, 1 changeover contact, input voltage 24 V DC

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2906285       |
| Packing unit                         | 20 pc         |
| Minimum order quantity               | 20 pc         |
| Sales key                            | CKF931        |
| Product key                          | CKF931        |
| GTIN                                 | 4055626066943 |
| Weight per piece (including packing) | 12.4 g        |
| Weight per piece (excluding packing) | 12.3 g        |
| Customs tariff number                | 85364190      |
| Country of origin                    | AT            |

# REL-MR-BL- 24DC/21HC - Single relay



2906285

<https://www.phoenixcontact.com/gb/products/2906285>

## Technical data

### Product properties

|                         |                           |
|-------------------------|---------------------------|
| Product type            | Single relay              |
| Operating mode          | 100% operating factor     |
| Mechanical service life | 1x 10 <sup>7</sup> cycles |

### Insulation characteristics

|            |                  |
|------------|------------------|
| Insulation | Basic insulation |
|------------|------------------|

### Insulation characteristics

|                      |                  |
|----------------------|------------------|
| Insulation           | Basic insulation |
| Overvoltage category | III              |
| Pollution degree     | 3                |

### Electrical properties

|                                                 |                                          |
|-------------------------------------------------|------------------------------------------|
| Service life electrical                         | see diagram                              |
| Maximum power dissipation for nominal condition | 0.4 W                                    |
| Test voltage (Winding/contact)                  | 5 kV AC (50 Hz, 1 min., winding/contact) |
| Rated insulation voltage                        | 250 V AC                                 |
| Rated surge voltage                             | 4 kV                                     |

### Input data

#### Coil side

|                                         |                       |
|-----------------------------------------|-----------------------|
| Nominal input voltage U <sub>N</sub>    | 24 V DC               |
| Input voltage range                     | 16.8 V DC ... 54 V DC |
| Drive and function                      | monostable            |
| Drive (polarity)                        | non-polarized         |
| Typical input current at U <sub>N</sub> | 17 mA                 |
| Typical response time                   | 8 ms                  |
| Typical release time                    | 6 ms                  |

### Output data

#### Switching

|                             |                                       |
|-----------------------------|---------------------------------------|
| Contact switching type      | 1 changeover contact                  |
| Type of switch contact      | Single contact                        |
| Contact material            | AgNi                                  |
| Maximum switching voltage   | 250 V AC/DC                           |
| Minimum switching voltage   | 5 V (At 24 mA)                        |
| Limiting continuous current | 16 A                                  |
| Maximum inrush current      | 30 A (300 ms)                         |
| Min. switching current      | 10 mA (at 12 V)<br>384 W (at 24 V DC) |

# REL-MR-BL- 24DC/21HC - Single relay




2906285  
<https://www.phoenixcontact.com/gb/products/2906285>

|                                       |                        |
|---------------------------------------|------------------------|
| Interrupting rating (ohmic load) max. | 58 W (at 48 V DC)      |
|                                       | 48 W (at 60 V DC)      |
|                                       | 50 W (at 110 V DC)     |
|                                       | 80 W (at 220 V DC)     |
|                                       | 4000 VA (for 250 V AC) |
| Switching capacity                    | 2 A (at 24 V, DC13)    |
|                                       | 1.5 A (at 230 V, AC15) |

## Connection data

|                   |                   |
|-------------------|-------------------|
| Connection method | Solder connection |
|-------------------|-------------------|

## Dimensions

|                     |                                                                                    |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 12.7 mm                                                                            |
| Height              | 29 mm                                                                              |
| Depth               | 15.7 mm                                                                            |

## Material specifications

|       |                   |
|-------|-------------------|
| Color | orange (RAL 2003) |
|-------|-------------------|

## Environmental and real-life conditions

|                                         |                  |
|-----------------------------------------|------------------|
| Ambient conditions                      |                  |
| Degree of protection                    | RT II            |
| Ambient temperature (operation)         | -40 °C ... 85 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |

## Standards and regulations


|                       |            |
|-----------------------|------------|
| Standards/regulations | IEC 60664  |
|                       | EN 61810-1 |

## Mounting


|                   |                  |
|-------------------|------------------|
| Mounting type     | Plug-in mounting |
| Mounting position | any              |


## Drawings

Circuit diagram



Diagram





Permissible humidity for operation and storage.


The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures  $\leq 0^\circ\text{C}$  must be prevented

Area B: Condensation at ambient temperatures  $> 0^\circ\text{C}$  must be prevented


On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature  $\leq 25^\circ\text{C}$ .

Drilling plan/solder pad geometry



Basic pitch 2.5 mm


Diagram




- ① 250 V AC, ohmic load (DC coils)
- ② 250 V AC, ohmic load (AC coils)

Electrical service life

Dimensional drawing





- ① DC coils
- ② AC coils

Operating voltage range

# REL-MR-BL- 24DC/21HC - Single relay



2906285

<https://www.phoenixcontact.com/gb/products/2906285>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2906285>



**cUL Recognized**  
Approval ID: FILE E 228652



**UL Recognized**  
Approval ID: FILE E 228652



**EAC**  
Approval ID: TR\_TS\_D\_00573\_c

**cULus Recognized**

# REL-MR-BL- 24DC/21HC - Single relay



2906285

<https://www.phoenixcontact.com/gb/products/2906285>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27371601 |
| ECLASS-12.0 | 27371601 |
| ECLASS-13.0 | 27371601 |

### ETIM

|          |          |
|----------|----------|
| ETIM 8.0 | EC001437 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

# REL-MR-BL- 24DC/21HC - Single relay



2906285

<https://www.phoenixcontact.com/gb/products/2906285>

## Environmental product compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

# REL-MR-BL- 24DC/21HC - Single relay



2906285

<https://www.phoenixcontact.com/gb/products/2906285>


## Mandatory accessories

### ECOR-1-BSC2-RT/2X21 - Relay base

1027546

<https://www.phoenixcontact.com/gb/products/1027546>

ECOR-1... relay base, for miniature power relays or miniature switching relays with 1 or 2 changeover contacts, bolt connection, for mounting on NS 35/7,5.



### ECOR-1-BSC3/2X21 - Relay base

2907518

<https://www.phoenixcontact.com/gb/products/2907518>

ECOR-1... relay base, for miniature power relay or miniature switching relay with 1 or 2 changeover contacts, screw connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5



Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)