

Spring-loaded tooling pin

GFS-6,00-1,50-RD-25-06,5-B

Item 20889



ingun[®]

Partner for Future Technology

- Trusted tooling pins for reliable positioning of the PCB via the tooling holes
- Spring-loaded design
- Low tolerances
- Various types for easy mounting in pressure plate and probe plate



General data

Product group:	Tooling pins
Series:	FS-GF
Type:	Round with collar (D7.4 x 2)
Version:	KTP
Accessory type:	Customising accessory
RoHS-compliant:	RoHS-3;6c

Mounting hole

Mounting hole in CEM1:	6.47 - 6.48 mm [.254 - .255 in]
Mounting hole in FR4:	6.47 - 6.48 mm [.254 - .255 in]

Technical data

Stroke:	10 mm [.393 in]
Tip diameter:	6 mm [.236 in]
Force:	6 N [21.5 ozf]
Installation:	Plugged
Spring force:	6 N [21.5 ozf]
Length:	50 mm [1.96 in]
Tip height:	6 mm [.236 in]
Diameter:	7.4 mm [.291 in]
Pin diameter:	6.5 mm [.255 in]

Compatible with

Exchangeable kits version:	No limitations
MA exchangeable kits (ATS MA):	ATS MA2xx # 3xx # xxxx
Interchangeable kits (WS):	WS

INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 07/24_GB