


NBC-R4ACS/3,0-93K/OE - Patch cable



1112858

<https://www.phoenixcontact.com/gb/products/1112858>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, degree of protection: IP20, cable length: 3 m, number of positions: 4, 100 Mbps, CAT5, material: PP, connection method: Pierce connection, connection cross section: AWG 23-22, cable outlet: straight, PROFINET

Your advantages

- Perfect for industrial applications
- PUR cable for moving applications (bend)
- Worldwide approval with CE, UL, WEEE, and EAC
- Secure connection and disconnection with reliable locking clip protection
- Ideal EMC properties, thanks to 360° shielding
- Simultaneous power transmission with PoE++
- Resistant to shock and vibrations, thanks to robust molding
- High-speed data transmission with up to 100 Mbps (CAT5)

Commercial data

Item number	1112858
Packing unit	1 pc
Minimum order quantity	2 pc
Sales key	ABNABA
Product key	ABNABA
GTIN	4063151034269
Weight per piece (including packing)	216.5 g
Weight per piece (excluding packing)	213.847 g
Customs tariff number	85444210
Country of origin	PL

NBC-R4ACS/3,0-93K/OE - Patch cable



1112858

<https://www.phoenixcontact.com/gb/products/1112858>

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	PROFINET
Number of positions	4
Shielded	yes
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/2)	72 V
Rated current	1.75 A
Insulation resistance	> 1 TΩ
Contact resistance	< 20 mΩ
Transmission characteristics (category)	CAT5
Transmission speed	100 Mbps

Mechanical properties

Mechanical data

Insertion force per signal contact	50.00 N
Extraction force per signal contact	30 N

Material specifications

Flammability rating according to UL 94	V2
Housing material	PP
Contact material	CuSn6
Contact surface material	Ni/Au
Contact carrier material	PC

Dimensions

Width	13.8 mm
Height	14.8 mm
Length	45 mm

Connection data

Connection technology

Connection method	Pierce connection
-------------------	-------------------

Conductor connection

Connection method	Pierce connection
-------------------	-------------------

NBC-R4ACS/3,0-93K/OE - Patch cable



1112858

<https://www.phoenixcontact.com/gb/products/1112858>

Connector

Connection 1

Type	Plug straight RJ45
Shielded	yes
Handle color	black
Insertion/withdrawal cycles	≥ 750
Degree of protection	IP20

Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	3.00 m
--------------	--------

Sercos III [93K]

Dimensional drawing	
Shielded	yes
UL AWM Style	21694 (60 °C / 600 V)
Cable weight	68 kg/km
Cable type	Sercos III
Cable type (abbreviation)	93K
Signal type/category	Sercos CAT5 (IEC 11801), 100 Mbps
Cable structure	1x4xAWG22/7, SF/TQ
External cable diameter	6.50 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	signal red RAL 3020
Thickness, outer sheath	approx. 0.90 mm
Material, inner sheath	PVC
Conductor material	Tin-plated Cu litz wires
Conductor structure signal line	7x 0.25 mm
AWG signal line	22
Conductor cross section	4x 0.34 mm²
Material wire insulation	PE
Wire diameter incl. insulation	approx. 1.55 mm
Single wire, color	white, yellow, blue, orange
Type of pair shielding	Aluminum-lined polyester foil

NBC-R4ACS/3,0-93K/OE - Patch cable



1112858

<https://www.phoenixcontact.com/gb/products/1112858>

Overall twist	Star quad
Shielding	Tinned copper braided shield
Nominal voltage, cable	600 V
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)
Cable resistance	$\leq 120 \Omega/\text{km}$
Cable insulation resistance	$\geq 0.5 \text{ G}\Omega \cdot \text{km}$
Coupling resistance	$\leq 20.00 \text{ m}\Omega/\text{m}$ (at 10 Hz)
Wave impedance	$100 \Omega \pm 15 \Omega$ (at 100 MHz)
Signal runtime	5.3 ns/m
Minimum bending radius, fixed installation	3 x D
Minimum bending radius, flexible installation	7 x D
Resistance to oil	Resistant to oil to a limited extent
Flame resistance	according to UL 1685 (CSA FT 4)
Other resistance	UV resistant (According to UL 1581, Section 1200)
Ambient temperature (operation)	-40 °C ... 70 °C (Cable, flexible installation)
	-40 °C ... 70 °C (cable, fixed installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C (RJ45 connector)
Ambient temperature (storage/transport)	-40 °C ... 85 °C (RJ45 connector)

Standards and regulations

Standards/specifications	IEC 60603-7
--------------------------	-------------

NBC-R4ACS/3,0-93K/OE - Patch cable



1112858

<https://www.phoenixcontact.com/gb/products/1112858>

Classifications

ECLASS

ECLASS-11.0	27060308
ECLASS-12.0	27060308
ECLASS-13.0	27060307

ETIM

ETIM 9.0	EC002599
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%