

2940090

<https://www.phoenixcontact.com/gb/products/2940090>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay module, with soldered-in miniature switching relay, gold contact for small loads, 1 changeover contact, input voltage 24 V DC

Your advantages

- Integrated input circuit and interference suppression circuit

Commercial data

Item number	2940090
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	CK6141
Product key	CK6141
Catalog page	Page 134 (IF-2011)
GTIN	4017918079864
Weight per piece (including packing)	41.076 g
Weight per piece (excluding packing)	38.01 g
Customs tariff number	85364190
Country of origin	DE

EMG 10-REL/KSR-G 24/21-LC AU - Relay Module



2940090

<https://www.phoenixcontact.com/gb/products/2940090>

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Relay Module
Product family	EMG
Application	Universal
Operating mode	100% operating factor
Mechanical service life	approx. 2×10^7 cycles

Insulation characteristics

Insulation	Basic insulation
------------	------------------

Insulation characteristics

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

Electrical properties

Maximum power dissipation for nominal condition	0.5 W
Test voltage (Winding/contact)	4 kV AC (50 Hz, 1 min., winding/contact)

Input data

Coil side

Nominal input voltage U_N	24 V DC
Input voltage range	21.6 V DC ... 26.4 V DC (20 °C)
Drive and function	monostable
Drive (polarity)	polarized
Typical input current at U_N	21 mA
Typical response time	7 ms
Typical release time	11 ms
Protective circuit	Reverse polarity protection; Polarity protection diode Freewheeling diode; Freewheeling diode
Operating voltage display	Yellow LED

Output data

Switching

Contact switching type	1 changeover contact
Type of switch contact	Double contact

EMG 10-REL/KSR-G 24/21-LC AU - Relay Module



2940090

<https://www.phoenixcontact.com/gb/products/2940090>

Contact material	AgPd60, hard gold-plated
Maximum switching voltage	30 V AC
	36 V DC
Limiting continuous current	0.5 A
Maximum inrush current	0.2 A
Interrupting rating (ohmic load) max.	5 W (at 24 V DC)

Switching: when the gold layer is destroyed

Note	the following values are applicable if a gold layer is destroyed
Maximum switching voltage	125 V AC
	150 V DC
Limiting continuous current	2 A
Maximum inrush current	2 A
Interrupting rating (ohmic load) max.	29 W (at 24 V DC)
	29 W (at 48 V DC)
	29 W (at 60 V DC)

Connection data

Coil side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section rigid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12

Contact side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section rigid	0.2 mm ² ... 4 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross section AWG	24 ... 12

Dimensions

Width	10.6 mm
Height	75 mm
Depth	62.5 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

EMG 10-REL/KSR-G 24/21-LC AU - Relay Module



2940090

<https://www.phoenixcontact.com/gb/products/2940090>

Ambient conditions

Ambient temperature (operation)	-20 °C ... 40 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	IEC 60664
	EN 50178

Mounting

Mounting type	DIN rail mounting
Assembly instructions	in rows with zero spacing
Mounting position	any

EMG 10-REL/KSR-G 24/21-LC AU - Relay Module

2940090

<https://www.phoenixcontact.com/gb/products/2940090>



Drawings

Connection diagram



EMG 10-REL/KSR-G 24/21-LC AU - Relay Module

2940090

<https://www.phoenixcontact.com/gb/products/2940090>



Circuit diagram



EMG 10-REL/KSR-G 24/21-LC AU - Relay Module



2940090

<https://www.phoenixcontact.com/gb/products/2940090>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2940090>



cUL Recognized
Approval ID: FILE E 238705



UL Recognized
Approval ID: FILE E 238705



EAC
Approval ID: TR_TS_D_00573_c



EAC
Approval ID: RU*C-DE.*08.B.00010

cULus Recognized

EMG 10-REL/KSR-G 24/21-LC AU - Relay Module



2940090

<https://www.phoenixcontact.com/gb/products/2940090>

Classifications

ECLASS

ECLASS-11.0	27371601
ECLASS-12.0	27371601
ECLASS-13.0	27371601

ETIM

ETIM 9.0	EC001437
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

EMG 10-REL/KSR-G 24/21-LC AU - Relay Module



2940090

<https://www.phoenixcontact.com/gb/products/2940090>

Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

EMG 10-REL/KSR-G 24/21-LC AU - Relay Module



2940090

<https://www.phoenixcontact.com/gb/products/2940090>

Accessories

EMG-SGKS 10 - Marking material

2947585

<https://www.phoenixcontact.com/gb/products/2947585>



Equipment marker, narrow

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk