

AM2SS-EZ

Click to
ORDER
samples



SIP4 Package

The AM2SS-EZ is a 2W SIP4 DC/DC converter that offers great cost savings thanks to an improved manufacturing process. It also features excellent reliability and performance while offering a standard input voltage range of 5-24VDC as well as an output voltage of -24 to 24V. This compact SIP4 package will surely benefit your new system design.

This new series offers great operating temperatures, from -40 to 105°C with full power up to 85°C. Also, an isolation of 1500VDC or 3000VDC for improved reliability and system safety as well as a great 3,500,000h MTBF come standard.


The AM2SS-EZ is suitable for many applications such as industrial systems, portable equipment, and internet of things.

Features

- Continuous Short circuit protection
- Operating Temp: -40 °C to +105 °C
- Industry standard SIP4 or DIL8 pin-out
- Efficiency up to 89%
- Unregulated output
- Designed to Meet IEC62368, UL62368, EN62368



Summary



Training



Product Training Video
(click to open)



Press Release

Coming Soon!

Application Notes

Applications



Industrial



Portable Equipment



IoT

Models & Specifications



Model	Input Voltage (VDC)	Output Voltage (VDC)	Output Current max (mA)*	Isolation (VAC/VDC)	Maximum capacitive Load (μF)	Efficiency Typ. (%)
AM2SS-0505SEZ	5 (4.5-5.5)	5	400	1500	2400	84
AM2SS-0509SEZ	5 (4.5-5.5)	9	223	1500	820	85
AM2SS-0512SEZ	5 (4.5-5.5)	12	167	1500	470	85
AM2SS-0515SEZ	5 (4.5-5.5)	15	133	1500	220	86
AM2SS-0524SEZ	5 (4.5-5.5)	24	84	1500	100	87
AM2SS-1205SEZ	12 (10.8-13.2)	5	400	1500	2400	85
AM2SS-1209SEZ	12 (10.8-13.2)	9	223	1500	820	87
AM2SS-1212SEZ	12 (10.8-13.2)	12	167	1500	470	87
AM2SS-1215SEZ	12 (10.8-13.2)	15	133	1500	220	88
AM2SS-1224SEZ	12 (10.8-13.2)	24	84	1500	100	89
AM2SS-1505SEZ	15 (13.5-16.5)	5	400	1500	2400	85
AM2SS-1509SEZ	15 (13.5-16.5)	9	223	1500	820	87
AM2SS-1512SEZ	15 (13.5-16.5)	12	167	1500	470	87
AM2SS-1515SEZ	15 (13.5-16.5)	15	133	1500	220	88
AM2SS-1524SEZ	15 (13.5-16.5)	24	84	1500	100	89
AM2SS-2405SEZ	24 (21.6-26.4)	5	400	1500	2400	85
AM2SS-2409SEZ	24 (21.6-26.4)	9	223	1500	820	87
AM2SS-2412SEZ	24 (21.6-26.4)	12	167	1500	470	87
AM2SS-2415SEZ	24 (21.6-26.4)	15	133	1500	220	88
AM2SS-2424SEZ	24 (21.6-26.4)	24	84	1500	100	89
AM2SS-0505SH30EZ	5 (4.5-5.5)	5	400	3000	2400	84
AM2SS-0509SH30EZ	5 (4.5-5.5)	9	223	3000	820	85
AM2SS-0512SH30EZ	5 (4.5-5.5)	12	167	3000	470	85
AM2SS-0515SH30EZ	5 (4.5-5.5)	15	133	3000	220	86
AM2SS-0524SH30EZ	5 (4.5-5.5)	24	84	3000	100	87
AM2SS-1205SH30EZ	12 (10.8-13.2)	5	400	3000	2400	85
AM2SS-1209SH30EZ	12 (10.8-13.2)	9	223	3000	820	87
AM2SS-1212SH30EZ	12 (10.8-13.2)	12	167	3000	470	87
AM2SS-1215SH30EZ	12 (10.8-13.2)	15	133	3000	220	88
AM2SS-1224SH30EZ	12 (10.8-13.2)	24	84	3000	100	89
AM2SS-1505SH30EZ	15 (13.5-16.5)	5	400	3000	2400	85
AM2SS-1509SH30EZ	15 (13.5-16.5)	9	223	3000	820	87
AM2SS-1512SH30EZ	15 (13.5-16.5)	12	167	3000	470	87
AM2SS-1515SH30EZ	15 (13.5-16.5)	15	133	3000	220	88
AM2SS-1524SH30EZ	15 (13.5-16.5)	24	84	3000	100	89
AM2SS-2405SH30EZ	24 (21.6-26.4)	5	400	3000	2400	85
AM2SS-2409SH30EZ	24 (21.6-26.4)	9	223	3000	820	87
AM2SS-2412SH30EZ	24 (21.6-26.4)	12	167	3000	470	87
AM2SS-2415SH30EZ	24 (21.6-26.4)	15	133	3000	220	88
AM2SS-2424SH30EZ	24 (21.6-26.4)	24	84	3000	100	89

Input Specification

Parameters	Conditions	Typical	Maximum	Units
Filter	Capacitor			
Voltage Tolerance	Vo, Io Nom	±10		%

Isolation Specification

Parameters	Conditions	Typical	Maximum	Units
Tested I/O voltage	60 sec, leakage ≤ 1mA, SEZ models	1500		VDC
	60 sec, leakage ≤ 1mA, SH30EZ models	3000		VDC
Resistance	500VDC	>1000		MΩ
Capacitance	100kHz/0.1V	20		pF

Output Specification

Parameters	Conditions	Typical	Maximum	Units
Voltage Tolerance	100% Full Load		±5	%
Line Regulation	Per 1% Vin change	1.2		%
Load regulation	5V (10% To 100% F.L)	8	15	%
	9V (10% To 100% F.L)	6	10	%
	12V (10% To 100% F.L)	5	10	%
	15V (10% To 100% F.L)	4	10	%
	24V (10% To 100% F.L)	3	10	%
Ripple & Noise*	All Models	75	150	mV p-p

* Ripple and Noise are measured at 20MHz bandwidth. Please refer to the application note for specific details.

General Specifications


Parameters	Conditions	Typical	Maximum	Units
Switching frequency	Full load, nominal input @5Vin	215		KHz
	Full load, nominal input @others	250		KHz
Short circuit protection	Continuous			
Operating temperature		-40 to +105		°C
Storage temperature		-55 to +125		°C
Cooling	Free air convection			
Humidity	Non-condensing	>5	95	% RH
Case material	DAP			
Weight		1.5		g
Dimensions (L x W x H)		0.45 x 0.24 x 0.39 inches (11.50 x 6.00 x 10.00 mm)		
MTBF	3 500 000 hrs (MIL-HDBK -217F, t=+25°C) / Full Load			

NOTE: All specifications in this datasheet are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified.


Safety Specifications

Parameters		
Standards	EMI	CE CISPR32 / EN55032, class B with the recommended EMI circuit RE CISPR32 / EN55032, class B with the recommended EMI circuit
	Electrostatic Discharge Immunity	EN60601-1-2 (IEC 61000-4-2) Air ±8kV, Contact ±6kV perf. Criteria B

Derating



Typical application circuit




Vin	Cin
5VDC	4.7μF/25V
12VDC	2.2μF/25V
15VDC	2.2μF/25V
24VDC	1μF/50V

Single Vout	Cout
5VDC	10μF/16V
9VDC	2.2μF/16V
12VDC	2.2μF/25V
15VDC	1μF/25V
24VDC	1μF/50V

Dual Vout	Cout
±5VDC	±4.7μF/16V
±9VDC	±1μF/16V
±12VDC	±1μF/25V
±15VDC	±1μF/25V
±24VDC	±1μF/50V


Table 1

Recommended EMI circuit




Emissions	Input Voltage	Single
	C1/C2	4.7μF/50V
	CY	1nF/4kV
	Cout	Reference Cout in Table 1
	LDM	6.8μH

Dimensions



Pin Out Specifications	
Pin	Single
1	-V Input
2	+V Input
3	-V Output
4	+V Output

Note:
Unit: mm
General tolerances: ±0.25 mm



NOTE: 1. Datasheets are updated as needed and as such, specifications are subject to change without notice. Once printed or downloaded, datasheets are no longer controlled by Aimtec; refer to www.aimtec.com for the most current product specifications. 2. Product labels shown, including safety agency certifications on labels, may vary based on the date manufactured. 3. Mechanical drawings and specifications are for reference only. 4. All specifications are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified. 5. Aimtec may not have conducted destructive testing or chemical analysis on all internal components and chemicals at the time of publishing this document. CAS numbers and other limited information are considered proprietary and may not be available for release. 6. This product is not designed for use in critical life support systems, equipment used in hazardous environments, nuclear control systems or other such applications which necessitate specific safety and regulatory standards other the ones listed in this datasheet. 7. Warranty is in accordance with Aimtec's standard Terms of Sale available at www.aimtec.com.