

OV-24DC/350DC/1 - Semi-conductor relay



2982634

<https://www.phoenixcontact.com/gb/products/2982634>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Solid-state relay, for signal amplification and isolation of the control and load circuits, can be plugged in the solderable plug-in bases SIM-AMS or with PCB connection for mounting directly onto the PCB, input: 4.25-32 V DC, output: 1-350 V DC/1 A

Your advantages

- Compact dimensions
- No electromagnetic interference
- High test voltage of up to 4 kV between control and load circuits
- No wear, even at high switching frequencies
- Electrically insulated housing
- No contact bounce – no movable parts
- Switching power of up to 350 V DC/1 A, 60 V DC/4 A or 480 V AC/5 A

Commercial data

Item number	2982634
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	CK7121
Product key	CK7121
Catalog page	Page 558 (C-7-2013)
GTIN	4046356131988
Weight per piece (including packing)	25.35 g
Weight per piece (excluding packing)	23 g
Customs tariff number	85362010
Country of origin	CN

OV-24DC/350DC/1 - Semi-conductor relay



2982634

<https://www.phoenixcontact.com/gb/products/2982634>

Technical data

Product properties

Product type	Single solid-state relay
Operating mode	100% operating factor

Insulation characteristics

Insulation	Basic insulation
------------	------------------

Insulation characteristics

Insulation	Basic insulation
------------	------------------

Electrical properties

Test voltage (Input/output)	4 kV (50 Hz, 1 min., input/output)
-----------------------------	------------------------------------


Input data

Nominal input voltage U_N	24 V DC
Input voltage range	4.25 V DC ... 32 V DC
Switching threshold "0" signal, voltage	< 1 V DC
Switching threshold "1" signal voltage	> 3.3 V DC
Typical input current at U_N	15 mA
Typical response time	< 100 μ s
Typical turn-off time	< 250 μ s
Transmission frequency	100 Hz

Output data

Design of digital output	electronic
Output voltage range	1 V DC ... 350 V DC
Limiting continuous current	1 A (see derating curve)
Min. load current	1 mA
Leakage current	100 μ A
Surge current	20 A ($t_p = 1$ s)
Voltage drop at max. limiting continuous current	0.5 V
Output circuit	2-conductor
Protective circuit	Reverse polarity protection; Polarity protection diode

Dimensions

Dimensional drawing	
Width	10.5 mm

OV-24DC/350DC/1 - Semi-conductor relay



2982634

<https://www.phoenixcontact.com/gb/products/2982634>

Height	43 mm
Depth	25.4 mm

Material specifications

Color	black (RAL 9005)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
Ambient temperature (storage/transport)	-20 °C ... 80 °C

Approvals

UKCA

Certificate	UKCA-compliant
-------------	----------------

Standards and regulations


Standards/regulations	EN 61000-4-2
	EN 61000-4-3
	EN 61000-4-4
	EN 55011

Mounting


Assembly instructions	Can be aligned with > 9 mm spacing
Mounting position	any

Drawings

Circuit diagram




Diagram



OV-24DC/350DC/1 - Semi-conductor relay

2982634

<https://www.phoenixcontact.com/gb/products/2982634>



OV-24DC/350DC/1 - Semi-conductor relay



2982634

<https://www.phoenixcontact.com/gb/products/2982634>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2982634>



cUL Recognized
Approval ID: FILE E 195083



UL Recognized
Approval ID: FILE E 195083



EAC
Approval ID: TR_TS_D_00573_c



EAC
Approval ID: RU*C-DE.*08.B.00010

cULus Recognized

OV-24DC/350DC/1 - Semi-conductor relay



2982634

<https://www.phoenixcontact.com/gb/products/2982634>

Classifications

ECLASS

ECLASS-11.0	27371604
ECLASS-12.0	27371604
ECLASS-13.0	27371604

ETIM

ETIM 8.0	EC001504
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

OV-24DC/350DC/1 - Semi-conductor relay



2982634

<https://www.phoenixcontact.com/gb/products/2982634>

Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk