

OV-24DC/480AC/5 - Semi-conductor relay



2982650

<https://www.phoenixcontact.com/gb/products/2982650>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Solid-state relay, for signal amplification and isolation of the control and load circuits, can be plugged in the solderable plug-in bases SIM-AMS or with PCB connection for mounting directly onto the PCB, input: 4-32 V DC, output: 12-530 V AC/ 5 A

Your advantages

- Compact dimensions
- No wear, even at high switching frequencies
- No electromagnetic interference
- High test voltage of up to 4 kV between control and load circuits
- No contact bounce – no movable parts
- Electrically insulated housing
- Switching power of up to 350 V DC/1 A, 60 V DC/4 A or 480 V AC/5 A

Commercial data

Item number	2982650
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	CK7121
Product key	CK7121
Catalog page	Page 559 (C-7-2013)
GTIN	4046356131667
Weight per piece (including packing)	25.34 g
Weight per piece (excluding packing)	24.7 g
Customs tariff number	85362010
Country of origin	CN

OV-24DC/480AC/5 - Semi-conductor relay



2982650

<https://www.phoenixcontact.com/gb/products/2982650>

Technical data

Product properties

Product type	Single solid-state relay
Operating mode	100% operating factor

Insulation characteristics

Insulation	Basic insulation
------------	------------------

Insulation characteristics

Insulation	Basic insulation
------------	------------------

Electrical properties

Test voltage (Input/output)	4 kV (50 Hz, 1 min., input/output)
-----------------------------	------------------------------------

Input data

Nominal input voltage U_N	24 V DC
Input voltage range	4 V DC ... 32 V DC
Switching threshold "0" signal, voltage	< 1.2 V DC
Switching threshold "1" signal voltage	> 3.5 V DC
Typical input current at U_N	10 mA
Typical response time	ms (maximum $\frac{1}{2}$ periods)
Typical turn-off time	ms (maximum $\frac{1}{2}$ periods)
Transmission frequency	25 Hz

Output data

Design of digital output	electronic
Output voltage range	12 V AC ... 530 V AC (45/65 Hz)
Limiting continuous current	5 A (see derating curve)
Min. load current	20 mA
Leakage current	< 1 mA
Surge current	80 A ($t_p = 20$ ms)
Phase angle $\cos \phi$ min	0.5
Max. load value	50 A ² s
Peak offstate voltage	1000 V (Periodic peak reverse voltage)
Voltage drop at max. limiting continuous current	1.2 V
Output circuit	2-conductor

Dimensions

OV-24DC/480AC/5 - Semi-conductor relay



2982650
<https://www.phoenixcontact.com/gb/products/2982650>

Dimensional drawing	
Width	10.5 mm
Height	43 mm
Depth	25.4 mm

Material specifications

Color	black (RAL 9005)
-------	------------------

Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Approvals

UKCA	
Certificate	UKCA-compliant

Standards and regulations

Standards/regulations	EN 61000-4-2
	EN 61000-4-3
	EN 61000-4-4
	EN 61000-4-5
	EN 61000-4-6
	EN 55011

Mounting

Assembly instructions	Can be aligned with > 20 mm spacing
Mounting position	any

OV-24DC/480AC/5 - Semi-conductor relay


2982650

<https://www.phoenixcontact.com/gb/products/2982650>




Drawings


Circuit diagram



Dimensional drawing



Diagram



OV-24DC/480AC/5 - Semi-conductor relay



2982650

<https://www.phoenixcontact.com/gb/products/2982650>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2982650>



cUL Recognized
Approval ID: FILE E 195083



UL Recognized
Approval ID: FILE E 195083



EAC
Approval ID: TR_TS_D_00573_c



EAC
Approval ID: RU*C-DE.*08.B.00010

cULus Recognized

OV-24DC/480AC/5 - Semi-conductor relay



2982650

<https://www.phoenixcontact.com/gb/products/2982650>

Classifications

ECLASS

ECLASS-11.0	27371604
ECLASS-12.0	27371604
ECLASS-13.0	27371604

ETIM

ETIM 8.0	EC001504
----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

OV-24DC/480AC/5 - Semi-conductor relay



2982650
<https://www.phoenixcontact.com/gb/products/2982650>

Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk