



Extension cable Jack (2.1x5.5x11-S to S/T) rc 0.8m, switch

Switch material	RoHS PC UL94V-2
Operating Temperature	0 ÷ 80[°C]
Length / cable type	0.8m / 20AWG - 2468
Max. load	5A
DC Connector	2.1x5.5x11
Weight	N.W.: 36g / pc
Packing plastic bag	Various [pcs] 80

