

Illuminated pushbutton with connector M12, Ø 22 mm,
stainless steel 316L, Series 82, Ø 25 mm, flush, Silver, IP65,
IP67, Cable 200 mm, 90°

82-665C.2154



<https://eao.com/p/ae61f199>

Your product:



82-665C.2154

Illuminated pushbutton with connector
M12, Ø 22 mm, stainless steel 316L,
Series 82, Ø 25 mm, flush, Silver, IP65,
IP67, Cable 200 mm, 90°

PRODUCT RANGE

HMI function: Illuminated pushbutton
Series: Series 82

FRONT

Front dimension: Ø 25 mm
Front bezel colour: Silver
Front bezel material: Stainless steel 316L

MOUNTING

Design: flush
Mounting cut-out: Ø 22 mm

OPERATING-/INDICATION PART

Shape of illumination: Ring
Lens illumination: illuminative
Lens colour: Silver
Lens shape: flush
Lens material: Stainless steel 316L
Lens optics: opaque
Illumination colour: White

ELECTRICAL CHARACTERISTICS

Electrical lifetime:	50 000 cycles of operation
Switching rating:	35 V AC/DC @ 0,5 A
Lumi. Intensity:	mcd
Operating voltage:	24 V AC/DC ± 10 %
Operation current:	7 mA

MECHANICAL CHARATERISTIC

Tightening torque:	0.5 ... 0.6 Nm
Terminal:	Cable 200 mm, 90°
Terminal lenght cable:	200
Contact material:	Silver
Switching action:	Maintained
Switching system:	Snap-action switching element
Total weight:	0.026 kg

AMBIENT CONDITION

IP front protection:	IP65, IP67
Operating temperature:	- 30 °C ... + 70 °C
Vibration resistance:	10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6

OTHER

Housing colour:	Silver
Housing material:	Stainless steel
Housing size:	19 mm
Symbol:	no symbol
Article number:	82-665C.2154