

# Interface block

## SB-P-PN-008-PK3

Item 27622




GO TO PRODUCT

**ingun**<sup>®</sup>

Partner for Future Technology

- Can be used in all test fixtures with internal or external pylon interface
- Consistently low contact loss
- High contact reliability and transmission quality
- Reliable transmission of compressed air

### INGUN SELECTION



#### General data

|                     |                              |
|---------------------|------------------------------|
| Product group:      | Interface blocks (SB)        |
| Series:             | SB-PN                        |
| Type:               | Pneumatic block              |
| Version:            | Device under test (DUT) side |
| Accessory type:     | Customising accessory        |
| Component assembly: | 8, fully loaded              |
| Weight:             | 0.035 kg [.077 lbs]          |
| Min. temperature:   | - 30 °C [- 86 °F]            |
| Max. temperature:   | + 120 °C [+ 248 °F]          |
| RoHS-compliant:     | RoHS-3                       |

#### Technical data

|                            |                                    |
|----------------------------|------------------------------------|
| Working distance:          | 15.1 +/- 0.5 mm [.594 +/- .019 in] |
| Centring pin:              | - mm                               |
| Connection:                | Plug nipple                        |
| Number of poles:           | 8                                  |
| Compressed air connection: | PK-3                               |
| Typical compressed air:    | 6 bar [87.0 psi]                   |
| Compressed air lock:       | No                                 |
| Compressed air quality:    | ISO 8573-1:2010                    |

#### Compatible with

|                                |                            |
|--------------------------------|----------------------------|
| Compatible mating part 1:      | SB-T-PN-008-PK3            |
| MA exchangeable kits (ATS MA): | ATS MAxx                   |
| VA exchangeable kits (ATS VA): | ATS VIN2040, ATS VIN2040-2 |
| PA exchangeable kits (ATS PA): | ATS PAZ100                 |

#### INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162  
78467, Constance, Germany  
Phone +49 7531 8105-0  
Customer hotline +49 7531 8105-888  
Fax +49 7531 8105-65  
info@ingun.com



Prices and delivery times on request.  
Technical changes reserved. 07/24\_GB