

Interface block


SB-T-PN-008-PK3

Item 27630



ingun[®]
Partner for Future Technology

- Can be used in all test fixtures with internal or external pylon interface
- Consistently low contact loss
- High contact reliability and transmission quality
- Reliable transmission of compressed air



General data

Product group:
Series:
Type:
Version:
Accessory type:
Component assembly:
Weight:
Min. temperature:
Max. temperature:
RoHS-compliant:

Interface blocks (SB)
SB-PN
Pneumatic block
Test system side
Customising accessory
8, fully loaded
0.07 kg [.154 lbs]
- 30 °C [- 86 °F]
+ 120 °C [+ 248 °F]
RoHS-3

Technical data

Working distance:
Centring pin:
Connection:
Number of poles:
Compressed air connection:
Typical compressed air:
Compressed air lock:
Compressed air quality:

15.1 +/- 0.5 mm [.594 +/- .019 in]
- mm
Plug nipple
8
PK-3
6 bar [87.0 psi]
No
ISO 8573-1:2010

Compatible with

Compatible mating part 1:
Manual test fixtures (MA):
Pylon receiver:

SB-P-PN-008-PK3
MA 21xx, MA 32xx
Pylon

INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 07/24_GB