


NBC-R4ACS/2,0-94C/OE - Patch cable



1113211

<https://www.phoenixcontact.com/gb/products/1113211>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, degree of protection: IP20, cable length: 2 m, number of positions: 8, 1 Gbps, CAT5, material: PP, connection method: Pierce connection, connection cross section: AWG 26-26, cable outlet: straight, Ethernet

Your advantages

- Perfect for industrial applications
- PUR cable for moving applications (bend)
- Worldwide approval with CE, UL, WEEE, and EAC
- Secure connection and disconnection with reliable locking clip protection
- Ideal EMC properties, thanks to 360° shielding
- Simultaneous power transmission with PoE++
- High-speed data transmission with up to 1 Gbps (CAT5)
- Resistant to shock and vibrations, thanks to robust molding

Commercial data

Item number	1113211
Packing unit	1 pc
Minimum order quantity	2 pc
Sales key	ABNABE
Product key	ABNABE
GTIN	4063151034597
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	124.435 g
Customs tariff number	85444210
Country of origin	PL

NBC-R4ACS/2,0-94C/OE - Patch cable



1113211

<https://www.phoenixcontact.com/gb/products/1113211>

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	Ethernet
Number of positions	8
Shielded	yes
Cable outlet	straight

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/2)	72 V
Rated current	1.5 A
Insulation resistance	> 1 TΩ
Contact resistance	< 20 mΩ
Transmission characteristics (category)	CAT5
Transmission speed	1 Gbps

Mechanical properties

Mechanical data

Insertion force per signal contact	50.00 N
Extraction force per signal contact	30 N

Material specifications

Flammability rating according to UL 94	V2
Housing material	PP
Contact material	CuSn6
Contact surface material	Ni/Au
Contact carrier material	PC
Outer sheath, material	PUR
Conductor material	Copper, bare

Dimensions

Width	13.8 mm
Height	14.8 mm
Length	44.2 mm

Connection data

Connection technology

Connection method	Pierce connection
-------------------	-------------------

NBC-R4ACS/2,0-94C/OE - Patch cable



1113211

<https://www.phoenixcontact.com/gb/products/1113211>

Conductor connection

Connection method	Pierce connection
-------------------	-------------------

Connector

Connection 1

Type	Plug straight RJ45
Shielded	yes
Handle color	black
Insertion/withdrawal cycles	≥ 750
Degree of protection	IP20

Connection 2

Type	free cable end
------	----------------

Cable/line

Cable length	2.00 m
--------------	--------

Ethernet drag chain CAT5, 4-pair [94C]

Dimensional drawing	
Shielded	yes
UL AWM Style	20963 (80°C/30 V)
Cable weight	57 kg/km
Cable type	Ethernet drag chain CAT5, 4-pair
Short symbol	9YC(ST)11Y
Cable type (abbreviation)	94C
Signal type/category	Ethernet CAT5 (IEC 11801), 1 Gbps
Cable structure	4x2xAWG26/19, S/UTP
External cable diameter	6.90 mm +0.1 mm ... 0.2 mm
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021
Thickness, outer sheath	0.85 mm
Conductor material	Bare Cu litz wires
Conductor structure signal line	19x 0.10 mm
AWG signal line	26
Conductor cross section	4x 2x 0.14 mm²
Material wire insulation	PP
Wire diameter incl. insulation	1 mm

NBC-R4ACS/2,0-94C/OE - Patch cable



1113211

<https://www.phoenixcontact.com/gb/products/1113211>

Single wire, color	white/blue-blue, white/orange-orange, white/green-green, white/brown-brown
Twisted pairs	2 cores to the pair
Overall twist	Four pairs and four fillers to the core
Shielding	Tinned copper braided shield
Optical shield covering	90 %
Nominal voltage, cable	≤ 100 V
Test voltage Core/Core	700 V (50 Hz, 1 min.)
Test voltage Core/Shield	700.00 V (50 Hz, 1 min.)
Cable insulation resistance	≥ 500 MΩ*km
Coupling resistance	≤ 100.00 mΩ/m (at 10 MHz)
Wave impedance	100 Ω ±5 Ω (at 100 MHz)
Loop resistance	≤ 290.00 Ω/km
Cable capacity	approx. 50 nF/km (at 1 kHz)
Signal runtime	5.3 ns/m
Tensile strength	≤ 100 N
Minimum bending radius, fixed installation	4 x D
Minimum bending radius, flexible installation	8 x D
Number of bending cycles	5000000
Minimum bending radius, drag chain applications	7,5 x D
Traversing rate	3 m/s
Acceleration	5 m/s²
Near end crosstalk attenuation (NEXT)	65.3 dB (with 1 MHz)
	56.3 dB (at 4 MHz)
	50.3 dB (at 10 MHz)
	47.2 dB (at 16 MHz)
	45.8 dB (at 20 MHz)
	42.9 dB (at 31.25 MHz)
	38.4 dB (at 62.5 MHz)
	35.3 dB (at 100 MHz)
Power-summated near end crosstalk attenuation (PSNEXT)	62.3 dB (with 1 MHz)
	53.3 dB (at 4 MHz)
	47.3 dB (at 10 MHz)
	44.2 dB (at 16 MHz)
	42.8 dB (at 20 MHz)
	39.9 dB (at 31.25 MHz)
	35.4 dB (at 62.5 MHz)
	32.3 dB (at 100 MHz)
Return attenuation (RL)	23 dB (at 4 MHz)
	24.1 dB (at 8 MHz)
	25 dB (at 10 MHz)
	25 dB (at 16 MHz)
	25 dB (at 20 MHz)
	23.6 dB (at 31.25 MHz)

NBC-R4ACS/2,0-94C/OE - Patch cable



1113211

<https://www.phoenixcontact.com/gb/products/1113211>

	21.5 dB (at 62.5 MHz)
	20.1 dB (at 100 MHz)
Halogen-free	according to IEC 60754-1
Resistance to oil	in accordance with EN 60811-2-1
Flame resistance	according to IEC 60332-1-2
Ambient temperature (operation)	-20 °C ... 80 °C (Cable, flexible installation)
	-40 °C ... 80 °C (cable, fixed installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C (RJ45 connector)
Ambient temperature (storage/transport)	-40 °C ... 85 °C (RJ45 connector)

Classifications

ECLASS

ECLASS-11.0	27440390
ECLASS-12.0	27440390
ECLASS-13.0	27060307

ETIM

ETIM 8.0	EC001121
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

NBC-R4ACS/2,0-94C/OE - Patch cable



1113211

<https://www.phoenixcontact.com/gb/products/1113211>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk