

Pushbutton Ø 19 mm silver contact

82-5162.2000



<https://eao.com/p/82-5162.2000>

Your product:



82-5162.2000
Pushbutton Ø 19 mm silver contact

FRONT

Front bezel material:	Stainless steel
Front bezel shape:	flush

MOUNTING

Mounting cut-out:	Ø 19 mm
-------------------	---------

OPERATING-/INDICATION PART

Lens illumination:	non illuminative
Lens colour:	Silver
Lens material:	Stainless steel
Lens shape:	raised
Lens optics:	opaque

ELECTRICAL CHARACTERISTICS

Thermal current Ith:	5 A
Rated Operational Voltage Ue:	250 VAC
Switching voltage and switching current:	according to IEC 60947-5-1 (Silver contacts) Service categorie AC-15 Voltage 24 VAC 35 VAC 110 VAC 220 VAC Switch rating DC service categorie DC-13 (Silver contacts) Voltage 24 VDC 35 VDC 110 VDC 220 VDC
	Current 1 A 1 A (M12 versio 1 A 0.5 A Current 0.7 A 0.5 A (M12 vers 0.2 A 0.1 A

according to UL 508 (Silver contacts)

$\cos\phi$ 0,75 ... 0,8

Voltage

120 VAC

240 VAC

24 VAC

Current

5 A

3 A

1 A

Electrical lifetime:	50 000 cycles of operation
Contacts:	1 C
Electric strength:	1500 VAC, 50 Hz 1 minute between life terminals and ground
Pollution degree:	2, according to EN IEC 60947-1
Rated insulation voltage U_i:	250 V

MECHANICAL CHARACTERISTIC

Switching system:	Snap-action switching element
Tightening torque:	0.5 ... 0.6 Nm, Screw terminal 0.1 Nm
Mechanical lifetime:	500 000 cycles of operation
Contact material:	Silver
Terminal:	Screw terminal
Operating Travel:	ca. 3 mm
Weight:	0.02 kg
Switching action:	Maintained
Operating force:	4 N ... 7 N

AMBIENT CONDITION

Storage temperature:	- 40 °C ... + 80 °C
Climate resistance:	Damp heat, 21 days according to IEC 60512-11
Vibration resistance:	10 ... 500 Hz, amplitude 1.5 mm p-p according to IEC 60068-2-6
Operating temperature:	- 30 °C ... + 70 °C
Shock resistance:	Max. 500 m / s ² as per IEC 60068-2-27


CERTIFICATE

Conformities:	CE, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)
Approbations:	CB, CCC, C UL, UL



OTHER

Short Description:

Pushbutton Ø 19 mm silver contact, Maintained, 1 C, Screw terminal, Stainless steel, Silver

Dimension drawings:

A = Solder terminal
B = Screw terminal

Mounting cut-outs:**Component layouts:****Wiring diagrams:**