

Actuator

46-
280S.1CV0.008



<https://testing.eao.com/p/46-280S.1CV0.008>

Your product:



46-280S.1CV0.008 Actuator

FRONT

Front form:	round
Front dimension:	Ø 29 mm
Front bezel colour:	Black
Front bezel material:	Plastic

MOUNTING

Design:	raised
Mounting cut-out:	Ø 22.3 mm

OPERATING-/INDICATION PART

Lever colour:	Black
Lever material:	plastic
Lever shape:	short
Lever bar colour:	White

ELECTRICAL CHARACTERISTICS

Protection class:	II
-------------------	----

MECHANICAL CHARACTERISTIC

Switching angle:	60° left / 60° right
Mechanical lifetime:	1 Mio. cycles of operation
Weight:	0.031 kg

Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Switching action:	Momentary - Rest - Momentary
Switching positions:	3 positions


AMBIENT CONDITION

IP front protection:	IP65
IK front protection:	IK06
Shock resistance:	30g, 18ms (EN-IEC 60068-2-27) 50g, 11ms (EN-IEC 60068-2-27)
Vibration resistance:	5g f= 2...500Hz (EN-IEC 60068-2-6)
Climate resistance:	+25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)
Operating temperature:	– 25 °C ... + 55 °C


CERTIFICATE

Approbations:	CSA, EAC, UL
Conformities:	CE
Standards:	CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

OTHER

Housing material:	Plastic
Short Description:	Actuator, Ø 22.3 mm, Ø 29 mm, non illuminative, Black, short, round, Black, Plastic, Momentary - Rest - Momentary, IP65, IK06
max. number of switching elements:	8
Housing colour:	Black
Switching positions:	

Dimension drawings:



Mounting cut-outs:

