

# Actuator

46-  
2234.4FK0.000



<https://testing.eao.com/p/46-2234.4FK0.000>

Your product:

---



## 46-2234.4FK0.000 Actuator

### FRONT

|                       |           |
|-----------------------|-----------|
| Front bezel material: | Aluminium |
| Front dimension:      | Ø 35 mm   |
| Front form:           | round     |
| Front bezel colour:   | Silver    |

### MOUNTING

|                   |           |
|-------------------|-----------|
| Design:           | flush     |
| Mounting cut-out: | Ø 30.5 mm |

### OPERATING-/INDICATION PART

|                    |              |
|--------------------|--------------|
| Lens colour:       | White        |
| Lens shape:        | flush        |
| Lens material:     | Plastic      |
| Lens illumination: | illuminative |
| Lens optics:       | transparent  |

### ELECTRICAL CHARACTERISTICS

|                   |   |
|-------------------|---|
| Protection class: | I |
|-------------------|---|

### MECHANICAL CHARACTERISTIC

|                   |            |
|-------------------|------------|
| Switching action: | Maintained |
| Weight:           | 0.035 kg   |

**Tightening torque:** 2 ... 3 Nm (17.7 ... 26.6 Lb-in)

**Mechanical lifetime:** 500 000 cycles of operation

## AMBIENT CONDITION

**Climate resistance:** +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

**Vibration resistance:** 5g f= 2...500Hz (EN-IEC 60068-2-6)

**Shock resistance:** 30g, 18ms (EN-IEC 60068-2-27)  
50g, 11ms (EN-IEC 60068-2-27)

**IP front protection:** IP65

**Operating temperature:** – 25 °C ... + 55 °C

**IK front protection:** IK04

## CERTIFICATE

**Standards:** CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

**Approbations:** CSA, UL

**Conformities:** CE

## OTHER


**Housing colour:** Black

**max. number of switching elements:** 4

**Housing material:** Plastic

**Short Description:** Actuator, Ø 30.5 mm, Ø 35 mm, flush, illuminative, White, Plastic, transparent, round, Silver, Aluminium, Maintained, IP65, IK04

**Mounting cut-outs:**



**Dimension drawings:**

