

Actuator

46-
2828.4CV0.001



<https://testing.eao.com/p/46-2828.4CV0.001>

Your product:



46-2828.4CV0.001 Actuator

FRONT

Front bezel colour:	Silver
Front dimension:	Ø 35 mm
Front bezel material:	Aluminium
Front form:	round

MOUNTING

Mounting cut-out:	Ø 30.5 mm
Design:	flush

OPERATING-/INDICATION PART

Lever colour:	Black
Lever bar colour:	White
Lever material:	plastic
Lever shape:	short

ELECTRICAL CHARACTERISTICS

Protection class:	I
-------------------	---

MECHANICAL CHARACTERISTIC

Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Mechanical lifetime:	1 Mio. cycles of operation
Weight:	0.039 kg

Switching positions:	2 positions
Switching action:	Maintained - Maintained
Switching angle:	90°

AMBIENT CONDITION


IP front protection:	IP65
Vibration resistance:	5g f= 2...500Hz (EN-IEC 60068-2-6)
Shock resistance:	30g, 18ms (EN-IEC 60068-2-27) 50g, 11ms (EN-IEC 60068-2-27)
Climate resistance:	+25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)
Operating temperature:	- 25 °C ... + 55 °C
IK front protection:	IK04

CERTIFICATE


Approbations:	CSA, UL
Standards:	CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508
Conformities:	CE

OTHER

max. number of switching elements:	6
Housing material:	Plastic
Housing colour:	Black
Short Description:	Actuator, Ø 30.5 mm, Ø 35 mm, non illuminative, Black, short, round, Silver, Aluminium, Maintained - Maintained, IP65, IK04
Dimension drawings:	



Mounting cut-outs:



Switching positions:

