

Actuator

46-
2844.1CV0.008



<https://testing.eao.com/p/46-2844.1CV0.008>

Your product:



46-2844.1CV0.008 Actuator

FRONT

Front bezel material:	Plastic
Front dimension:	Ø 29 mm
Front bezel colour:	Black
Front form:	round

MOUNTING

Design:	raised
Mounting cut-out:	Ø 22.3 mm

OPERATING-/INDICATION PART

Lever colour:	Black
Lever material:	plastic
Lever bar colour:	White
Lever shape:	short

ELECTRICAL CHARACTERISTICS

Protection class:	II
-------------------	----

MECHANICAL CHARACTERISTIC

Switching angle:	60° right
Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Weight:	0.027 kg

Switching positions:	2 positions
Mechanical lifetime:	1 Mio. cycles of operation
Switching action:	Rest - Momentary

AMBIENT CONDITION


Operating temperature:	- 25 °C ... + 55 °C
Shock resistance:	30g, 18ms (EN-IEC 60068-2-27) 50g, 11ms (EN-IEC 60068-2-27)
Vibration resistance:	5g f= 2...500Hz (EN-IEC 60068-2-6)
IK front protection:	IK06
Climate resistance:	+25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)
IP front protection:	IP65

CERTIFICATE


Conformities:	CE
Approbations:	CSA, EAC, UL
Standards:	CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

OTHER

Housing material:	Plastic
Short Description:	Actuator, Ø 22.3 mm, Ø 29 mm, non illuminative, Black, short, round, Black, Plastic, Rest - Momentary, IP65, IK06
Housing colour:	Black
max. number of switching elements:	8
Dimension drawings:	



Switching positions:	
-----------------------------	--



Mounting cut-outs:

