

Actuator

46-
290F.1000.7P8



<https://testing.eao.com/p/46-290F.1000.7P8>

Your product:



46-290F.1000.7P8 Actuator

FRONT

Front form:	round
Front dimension:	Ø 29 mm
Front bezel material:	Plastic
Front bezel colour:	Black

MOUNTING

Mounting cut-out:	Ø 22.3 mm
Design:	raised

ELECTRICAL CHARACTERISTICS

Protection class:	II
-------------------	----

MECHANICAL CHARACTERISTIC

Switching action:	Maintained (a) - Rest (a) - Maintained (a)
Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Release type:	Key release to unlock
Mechanical lifetime:	50 000 cycles of operation
Weight:	0.076 kg
Switching positions:	3 positions
Switching angle:	60° left / 60° right

AMBIENT CONDITION


Vibration resistance:	5g f= 2...500Hz (EN-IEC 60068-2-6)
Shock resistance:	30g, 18ms (EN-IEC 60068-2-27) 50g, 11ms (EN-IEC 60068-2-27)
Operating temperature:	– 25 °C ... + 55 °C
Climate resistance:	+25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)
IP front protection:	IP65
IK front protection:	IK06

CERTIFICATE


Standards:	CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508
Approbations:	CSA, EAC, UL
Conformities:	CE

OTHER

Housing material:	Plastic
Housing colour:	Black
max. number of switching elements:	8
Short Description:	Actuator, Ø 22.3 mm, Ø 29 mm, round, Black, Plastic, Maintained (a) - Rest (a) - Maintained (a), IP65, IK06, Key release to unlock
Switching positions:	



Dimension drawings:



Mounting cut-outs:

