

Actuator

46-
2925.1000.7P8



<https://testing.eao.com/p/46-2925.1000.7P8>

Your product:



46-2925.1000.7P8 Actuator

FRONT

Front dimension:	Ø 29 mm
Front bezel colour:	Black
Front bezel material:	Plastic
Front form:	round

MOUNTING

Mounting cut-out:	Ø 22.3 mm
Design:	raised

ELECTRICAL CHARACTERISTICS

Protection class:	II
-------------------	----

MECHANICAL CHARACTERISTIC

Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Weight:	0.076 kg
Release type:	Key release to unlock
Switching action:	Rest - Maintained (a)
Mechanical lifetime:	50 000 cycles of operation
Switching positions:	2 positions
Switching angle:	60° right

AMBIENT CONDITION


Shock resistance:	30g, 18ms (EN-IEC 60068-2-27) 50g, 11ms (EN-IEC 60068-2-27)
Operating temperature:	– 25 °C ... + 55 °C
IK front protection:	IK06
Vibration resistance:	5g f= 2...500Hz (EN-IEC 60068-2-6)
IP front protection:	IP65
Climate resistance:	+25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

CERTIFICATE


Conformities:	CE
Standards:	CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508
Approbations:	CSA, EAC, UL

OTHER

max. number of switching elements:	8
Short Description:	Actuator, Ø 22.3 mm, Ø 29 mm, round, Black, Plastic, Rest - Maintained (a), IP65, IK06, Key release to unlock
Housing material:	Plastic
Housing colour:	Black
Switching positions:	



Mounting cut-outs:



Dimension drawings:

