

Actuator

46-
290H.1000.7PD



<https://testing.eao.com/p/46-290H.1000.7PD>

Your product:



46-290H.1000.7PD Actuator

FRONT

Front dimension:	Ø 29 mm
Front form:	round
Front bezel material:	Plastic
Front bezel colour:	Black

MOUNTING

Design:	raised
Mounting cut-out:	Ø 22.3 mm

ELECTRICAL CHARACTERISTICS

Protection class:	II
-------------------	----

MECHANICAL CHARACTERISTIC

Release type:	Key release to unlock
Switching angle:	120°
Weight:	0.076 kg
Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Switching action:	Maintained (a) - Maintained (a)
Switching positions:	2 positions
Mechanical lifetime:	50 000 cycles of operation

AMBIENT CONDITION


IK front protection:	IK06
Vibration resistance:	5g f= 2...500Hz (EN-IEC 60068-2-6)
Shock resistance:	30g, 18ms (EN-IEC 60068-2-27) 50g, 11ms (EN-IEC 60068-2-27)
Operating temperature:	- 25 °C ... + 55 °C
IP front protection:	IP65
Climate resistance:	+25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

CERTIFICATE


Conformities:	CE
Standards:	CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508
Approbations:	CSA, EAC, UL

OTHER

Housing material:	Plastic
Short Description:	Actuator, Ø 22.3 mm, Ø 29 mm, round, Black, Plastic, Maintained (a) - Maintained (a), IP65, IK06, Key release to unlock
max. number of switching elements:	8
Housing colour:	Black
Switching positions:	



Mounting cut-outs:



Dimension drawings:

