

Holder

46-
2V00.000.000



<https://testing.eao.com/p/46-2V00.000.000>

Your product:



46-2V00.000.000 Holder

FRONT

Colour: Grey

ELECTRICAL CHARACTERISTICS

Protection class: II

MECHANICAL CHARACTERISTIC

Tightening torque: 0.8 ... 1 Nm for screw terminal

Weight: 0.016 kg

AMBIENT CONDITION

Shock resistance: 30g, 18ms (EN-IEC 60068-2-27)
50g, 11ms (EN-IEC 60068-2-27)

Vibration resistance: 5g f= 2...500Hz (EN-IEC 60068-2-6)

IP front protection: IP20

Climate resistance: +25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)

Operating temperature: – 25 °C ... + 55 °C

CERTIFICATE

Approbations: CSA, EAC, UL

Conformities: CE

Standards: CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

OTHER


Dimension: 38 mm x 30 mm

Short Description: Holder, Plastic

Material: Plastic

Colour RAL: 7016 RAL

Wiring diagrams:



Dimension drawings:

