

DC12V SMD5050 RGBW LED strip 60LEDs/M



Product Description :

This is a PWM control RGBW color LED strip without Pixel
 60pcs SMD 5050 4 in 1 RGBW LEDs per meter
 The cutting unit length is 50mm per section
 The PCB is made by 3 Ounce copper
 All soldering Pads are very large, allowing you to cut
 and reconnect very easy
 Both ends have 5pin bare wires for powering, common
 anode, black cable is DC+
 5meters/reel, 3M tape attached on backside of FPC
 IP rate: IP20, IP64, IP65, IP67




Product Datasheet

Product Number	S012060CB4PZ	Luminance/M	R: 106 G: 261 B: 59 W: 378lm
Operating Voltage	DC12V	Ra	80(90)
Power/M	19.2W	Beam Angle	120°
SMD Type	SMD 5050 4in1	Size (mm)	5000 * 12mm
LED Qty/M	60	IP Rate	IP20/IP64/IP65/IP67
Color	RGB+W:3000K/4000K/6000K	Operation Temperature	- 25 ~ 60 °C
Pixel/M	/	Material	FPC
Control	PWM	Cutting Length	50mm
Wavelength	R:620-625 G:520-525 B:460-465nm	Net Weight/Roll	0.13KG

Outline Dimension (unit: mm)


DC12V



◆ Order number

DC12V	RGB+W:3000K	White PCB	IP20	S012060CB4PZ/C1
DC12V	RGB+W:4000K	White PCB	IP20	S012060CB4PZ/C2
DC12V	RGB+W:6000K	White PCB	IP20	S012060CB4PZ/C3
DC12V	RGB+W:3000K	White PCB	IP65	S012060CB4PZ/C4
DC12V	RGB+W:4000K	White PCB	IP65	S012060CB4PZ/C5
DC12V	RGB+W:6000K	White PCB	IP65	S012060CB4PZ/C6

◆ Wiring diagram



◆ Strip IP Rate



◆ Accessories



Screw




Silicone clip



End cap

◆ Schematic diagram of maximum bending prevention



Note: The parameters are subject to change without notice!