

DC24V SMD5050 RGBW LED Strip 60LEDs/M



Product Description:


This is a PWM control RGBW color LED strip without Pixel
 60pcs SMD 5050 4 in 1 RGBW LEDs per meter,
 The cutting unit length is 100mm per section
 The PCB is made by 3 Ounce copper
 All soldering Pads are very large, allowing you to
 cut and reconnect very easy
 DC24V constant voltage operation
 Both ends have 5pin bare wires for powering,
 Common anode, black cable is DC+
 5meters/reel
 3M tape attached on backside of FPC
 3 different waterproof types IP64, IP65, IP67

Product Datasheet

Product Number	S012060CC4PZ	Luminance/M	R: 106 G: 261 B: 59 W: 378lm
Operating Voltage	DC24V	Ra	/
Power/M	19.2W	Beam Angle	120°
SMD Type	SMD 5050 4in1	Size (mm)	5000 * 12mm
LED Qty/M	60	IP Rate	IP20/IP64/IP65/IP67
Color	RGB+W:3000K/4000K/6000K	Operation Temperature	- 25 ~ 60 °C
Pixel/M	/	Material	FPC
Control	PWM	Cutting Length	100mm
Wavelength	R:620-625 G:520-525 B:460-465nm	Net Weight/Roll	0.13KG

Outline Dimension (unit: mm)


DC24V




◆ Order number

DC24V	RGB+W:3000K	White PCB	IP20	S012060CC4PZ/C1
DC24V	RGB+W:4000K	White PCB	IP20	S012060CC4PZ/C2
DC24V	RGB+W:6000K	White PCB	IP20	S012060CC4PZ/C3
DC24V	RGB+W:3000K	White PCB	IP65	S012060CC4PZ/C4
DC24V	RGB+W:4000K	White PCB	IP65	S012060CC4PZ/C5
DC24V	RGB+W:6000K	White PCB	IP65	S012060CC4PZ/C6

◆ Wiring diagram



◆ Strip IP Rate



◆ Accessories



Screw




Silicone clip



End cap

◆ Schematic diagram of maximum bending prevention



Note: The parameters are subject to change without notice!