



嘉尼企業股份有限公司 CANAL ELECTRONIC CO.,LTD.



ROCKER SWITCH MODEL: X7-H SERIES

RATING: 16A 12VDC




DIELECTRIC WITHSTAND VOLTAGE: 1500VAC 1 MINUTE

INSULATION RESISTANCE: 500VDC 100M Ω (MIN)

CONTACT RESISTANCE: 20m Ω INITIAL (MAX.)

ILLUMINATION: 12VDC

WATERPROOF GRADE: IP67



X=(0.8~3.0mm)

PANEL THICKNESS

NOTE: TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm .012/0.3$ (in/mm)

REVISION	DESCRIPTION	REVISED BY	TOLERANCES		ANGLE $\frac{1}{2}^\circ$		UNIT	mm	PART NAME	DWG NO
△			DRAWN BY	趙超	DESIGNED BY	蔡劍	SCALE	3/2	X7 SPEC DRAWING	
△	2021.03.30	整理圖面，重新出圖	CHECKED BY	達志各	APPROVED BY	蔡劍	DATE	2015.07.29	X7-H10F2N-1**D-1*WC	S6159B
△	2015.07.29	首次出圖								