





ROCKER SWITCH MODEL MR2 SERIES
RATING:16(8)A 125/250V~ (cURus / ENEC15)
16(8)A 250V~ T85 (CQC)
DIELECTRIC VOLTAGE-WITHSTAND:1500VAC FOR 1 MINUTE
INSULATION RESISTANCE: 500VDC 100MΩ (MIN.)
CONTACT RESISTANCE:20mΩ INITIAL (MAX.)



PANEL CUTOUT DIMENSION TABLE

NOTES: TOLERANCES UNLESS OTHERWISE SPECIFIED:±.012/0.3(in/mm)

REVISION	DESCRIPTION	REVISED BY	TOLERANCES		ANGLE 1/2°		UNIT	mm	PART NAME	MR2 SPEC DRAWING	DWG NO
			DRAWN BY	CHECKED BY	DESIGNED BY	APPROVED BY					
△			楊偉韶		蔡劍						S8601A
△											
△											
△											
△	2021.09.14	首次出圖	楊偉韶							MR2-110R5*-N*B-2BNC	