

NBC-R4ACS/2,0-93B/R4ACT - Patch cable



1113309

<https://www.phoenixcontact.com/gb/products/1113309>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, degree of protection: IP20, cable length: 2 m, number of positions: 4, 100 Mbps, CAT5, material: PP, connection method: Pierce connection, cable outlet: straight, PROFINET

Your advantages

- Compact angle
- Perfect for industrial applications
- PVC cable for flexible installations
- Worldwide approval with CE, UL, WEEE, and EAC
- Secure connection and disconnection with reliable locking clip protection
- Ideal EMC properties, thanks to 360° shielding
- Simultaneous power transmission with PoE++
- Resistant to shock and vibrations, thanks to robust molding
- High-speed data transmission with up to 100 Mbps (CAT5)

Commercial data

Item number	1113309
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ABNABA
Product key	ABNABA
GTIN	4063151036546
Weight per piece (including packing)	158 g
Weight per piece (excluding packing)	156.222 g
Customs tariff number	85444210
Country of origin	PL

NBC-R4ACS/2,0-93B/R4ACT - Patch cable



1113309

<https://www.phoenixcontact.com/gb/products/1113309>

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	PROFINET
Number of positions	4
Shielded	yes
Cable outlet	straight

Data management status

Article revision	02
------------------	----

Insulation characteristics

Overvoltage category	I
Degree of pollution	2

Electrical properties

Rated voltage (III/2)	72 V
Rated current	1.75 A
Insulation resistance	> 1 TΩ
Contact resistance	< 20 mΩ
Transmission characteristics (category)	CAT5
Transmission speed	100 Mbps

Mechanical properties

Mechanical data

Insertion force per signal contact	50.00 N
Extraction force per signal contact	30 N

Material specifications

Flammability rating according to UL 94	V2
Housing material	PP
Contact material	CuSn6
Contact surface material	Ni/Au
Contact carrier material	PC

Dimensions

Width	13.8 mm
Height	31.2 mm
Length	34 mm

Connection data

Connection technology

Connection method	Pierce connection
-------------------	-------------------

NBC-R4ACS/2,0-93B/R4ACT - Patch cable



1113309

<https://www.phoenixcontact.com/gb/products/1113309>

Conductor connection

Connection method	Pierce connection
-------------------	-------------------

Connector

Connection 1

Type	Plug straight RJ45
Shielded	yes
Handle color	black
Insertion/withdrawal cycles	≥ 750
Degree of protection	IP20

Connection 2

Type	Plug top RJ45
Handle color	black
Insertion/withdrawal cycles	≥ 750
Degree of protection	IP20

Cable/line

Cable length	2.00 m
--------------	--------

PROFINET PVC stranded CAT5 [93B]

Dimensional drawing	
Shielded	yes
UL AWM Style	21694
Cable weight	67 kg/km
Cable type	PROFINET PVC stranded CAT5
Short symbol	2YY(ST)CY
Cable type (abbreviation)	93B
Signal type/category	PROFINET CAT5 (IEC 11801), 100 Mbps EtherCAT® CAT5 (IEC 11801), 100 Mbps
Cable structure	1x4xAWG22/7, SF/TQ
External cable diameter	6.50 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	green RAL 6018
Thickness, outer sheath	approx. 0.90 mm
Material, inner sheath	PVC
Conductor material	Tin-plated Cu litz wires

NBC-R4ACS/2,0-93B/R4ACT - Patch cable



1113309

<https://www.phoenixcontact.com/gb/products/1113309>

Conductor structure signal line	7x 0.25 mm
AWG signal line	22
Conductor cross section	4x 0.34 mm ²
Material wire insulation	PE
Wire diameter incl. insulation	1.55 mm
Single wire, color	white, yellow, blue, orange
Overall twist	Star quad
Shielding	Aluminum-coated foil, tinned copper braided shield
Optical shield covering	85 %
Nominal voltage, cable	600 V
Test voltage Core/Core	2000 V (50 Hz, 1 min.)
Test voltage Core/Shield	2000.00 V (50 Hz, 1 min.)
Cable insulation resistance	≥ 500 MΩ*km
Coupling resistance	≤ 20.00 mΩ/m (at 10 MHz)
Wave impedance	100 Ω ±15 Ω (at 100 MHz)
Loop resistance	≤ 120.00 Ω/km
Signal runtime	5.3 ns/m
Signal speed	0.66 c
Minimum bending radius, fixed installation	3 x D
Minimum bending radius, flexible installation	7 x D
Near end crosstalk attenuation (NEXT)	80 dB (with 1 MHz)
	76 dB (at 4 MHz)
	70 dB (at 10 MHz)
	65 dB (at 16 MHz)
	63 dB (at 20 MHz)
	60 dB (at 31.25 MHz)
	55 dB (at 62.5 MHz)
	50 dB (at 100 MHz)
Resistance to oil	Resistant to oil to a limited extent
Flame resistance	according to UL 1685 (CSA FT 4)
Other resistance	UV resistant (according to UL 1581, Section 1200)
Ambient temperature (operation)	-40 °C ... 70 °C (Cable, flexible installation)
	-40 °C ... 70 °C (cable, fixed installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 85 °C (RJ45 connector)
Ambient temperature (storage/transport)	-40 °C ... 85 °C (RJ45 connector)

Standards and regulations

Standards/specifications	IEC 60603-7
--------------------------	-------------

NBC-R4ACS/2,0-93B/R4ACT - Patch cable



1113309

<https://www.phoenixcontact.com/gb/products/1113309>

Classifications

ECLASS

ECLASS-11.0	27060308
ECLASS-12.0	27060308
ECLASS-13.0	27060307

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

NBC-R4ACS/2,0-93B/R4ACT - Patch cable



1113309

<https://www.phoenixcontact.com/gb/products/1113309>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk