




Multifunction display for monitoring analogue standard signals

DISPLAY/AX460/PNP OUT/AC/DC



Product characteristics		
Dimensions	[mm]	48 x 112 x 116
Application		
Application	displaying and monitoring analogue signals; e.g. pressure sensors, temperature sensors or flow sensors	
Electrical data		
Frequency AC	[Hz]	50...60
Operating voltage	[V]	115...230 AC / 18...30 DC
Current consumption	[mA]	100
Inputs / outputs		
Number of inputs and outputs	Number of analogue inputs: 2; Number of digital outputs: 4	
Inputs		
Number of analogue inputs	2; (Spannungs- oder Stromeingang)	
Analogue input (current)	[mA]	0...20
Analogue input (voltage)	[V]	-10...10
Resolution of analogue input	16 bit	
Precision analogue input	[%]	0,1
Outputs		
Number of digital outputs	4	
Overload protection	yes	
Operating conditions		
Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...70
Protection	IP 65	
Protection rating terminals	IP 20	
Tests / approvals		
EMC	EN 61000-6-2	
	EN 61000-6-3	
	EN 61000-6-4	




Multifunction display for monitoring analogue standard signals

DISPLAY/AX460/PNP OUT/AC/DC

Mechanical data		
Weight	[g]	350.5
Type of mounting		panel cutout: 91 x 43 mm
Dimensions	[mm]	48 x 112 x 116
Materials		Noryl UL94-V-0

Displays / operating elements		
Display	colour display	full graphic LCD display, touch screen

Electrical connection		
screw terminals:		
Connection		



NC not used