

Actuator

46-
2819.1EX0.008



<https://testing.eao.com/p/46-2819.1EX0.008>

Your product:



46-2819.1EX0.008 Actuator

FRONT

Front bezel colour:	Black
Front bezel material:	Plastic
Front form:	round
Front dimension:	Ø 29 mm

MOUNTING

Mounting cut-out:	Ø 22.3 mm
Design:	raised

OPERATING-/INDICATION PART

Lever material:	plastic
Lever shape:	short
Lever colour:	Black
Lever bar colour:	Green

ELECTRICAL CHARACTERISTICS

Protection class:	II
-------------------	----

MECHANICAL CHARACTERISTIC

Switching angle:	60° left / 60° right
Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Switching action:	Maintained - Rest - Maintained

Mechanical lifetime:	1 Mio. cycles of operation
Switching positions:	3 positions
Weight:	0.027 kg

AMBIENT CONDITION


Vibration resistance:	5g f= 2...500Hz (EN-IEC 60068-2-6)
Climate resistance:	+25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)
IK front protection:	IK06
IP front protection:	IP65
Operating temperature:	– 25 °C ... + 55 °C
Shock resistance:	30g, 18ms (EN-IEC 60068-2-27) 50g, 11ms (EN-IEC 60068-2-27)

CERTIFICATE


Approbations:	CSA, EAC, UL
Conformities:	CE
Standards:	CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

OTHER

Short Description:	Actuator, Ø 22.3 mm, Ø 29 mm, non illuminative, Black, short, round, Black, Plastic, Maintained - Rest - Maintained, IP65, IK06
Housing material:	Plastic
Housing colour:	Black
max. number of switching elements:	8
Dimension drawings:	



Mounting cut-outs:



Switching positions:

