

Actuator

46-
2Y49.101C.000



<https://testing.eao.com/p/46-2Y49.101C.000>

Your product:



46-2Y49.101C.000 Actuator

FRONT

Front bezel material:	Plastic
Front dimension:	Ø 29 mm
Front form:	round
Front bezel colour:	Black

MOUNTING

Mounting cut-out:	Ø 22.3 mm
Design:	raised

ELECTRICAL CHARACTERISTICS

Contact resistance:	<30mOhm
Insulation voltage:	>100MOhm
Electrical lifetime:	>50 000 h

MECHANICAL CHARACTERISTIC

Terminal:	USB 3.0 socket type A-A
Weight:	0.024 kg
Mechanical lifetime:	>15 000 insertion cycles
Tightening torque:	1 ... 2.5 Nm (8.8 ... 22.1 Lb-in)

AMBIENT CONDITION

Operating temperature:	- 25 °C ... + 55 °C
------------------------	---------------------

IP front protection: IP20 / IP66 with cap closed (IEC-EN60529)

Shock resistance: 30g, 18ms (EN-IEC 60068-2-27)

Vibration resistance: 5g f= 2...500Hz (EN-IEC 60068-2-6)

Climate resistance: +40°C-92%RH

CERTIFICATE

Standards: CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508, USB 3.0 type A

Conformities: CE


OTHER

Short Description: Actuator, Ø 22.3 mm, Ø 29 mm, round, Black, Plastic, USB 3.0 socket type A-A, IP20 / IP66 with cap closed (IEC-EN60529)

Housing material: Plastic

Housing colour: Black

Dimension drawings:



Mounting cut-outs:

