

Actuator

46-
2W19.1CN0.004



<https://testing.eao.com/p/46-2W19.1CN0.004>

Your product:



46-2W19.1CN0.004 Actuator

FRONT

Front form:	round
Front dimension:	Ø 30 mm
Front bezel colour:	Black
Front bezel material:	Plastic

MOUNTING

Mounting cut-out:	Ø 22.3 mm
Design:	raised

OPERATING-/INDICATION PART

Lever colour:	White
Lever material:	plastic
Lever shape:	short
Lever bar colour:	White

ELECTRICAL CHARACTERISTICS

Protection class:	II
-------------------	----

MECHANICAL CHARACTERISTIC

Switching angle:	45° left / 45° right
Mechanical lifetime:	1 Mio. cycles of operation
Weight:	0.027 kg

Switching positions:	3 positions
Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Switching action:	Maintained - Rest - Maintained

AMBIENT CONDITION


Shock resistance:	30g, 18ms (EN-IEC 60068-2-27)
Vibration resistance:	5g f= 2...500Hz (EN-IEC 60068-2-6)
IP front protection:	IP65
IK front protection:	IK03
Climate resistance:	+25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)
Operating temperature:	- 25 °C ... + 55 °C

CERTIFICATE


Conformities:	CE
Standards:	CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508

OTHER

max. number of switching elements:	2
Short Description:	Actuator, Ø 22.3 mm, Ø 30 mm, illuminative, White, short, round, Black, Plastic, Maintained - Rest - Maintained, IP65, IK03
Housing colour:	Black
Housing material:	Plastic
Switching positions:	



Dimension drawings:



Mounting cut-outs:

