

Actuator

46-
2W28.4CE0.001



<https://testing.eao.com/p/46-2W28.4CE0.001>

Your product:



46-2W28.4CE0.001 Actuator

FRONT

Front form:	round
Front bezel material:	Aluminium
Front dimension:	Ø 35 mm
Front bezel colour:	Silver

MOUNTING

Design:	flush
Mounting cut-out:	Ø 30.5 mm

OPERATING-/INDICATION PART

Lever colour:	Red
Lever shape:	short
Lever material:	plastic
Lever bar colour:	White

ELECTRICAL CHARACTERISTICS

Protection class:	I
-------------------	---

MECHANICAL CHARACTERISTIC

Switching action:	Maintained - Maintained
Mechanical lifetime:	1 Mio. cycles of operation
Switching positions:	2 positions

Tightening torque:	2 ... 3 Nm (17.7 ... 26.6 Lb-in)
Weight:	0.036 kg
Switching angle:	90°


AMBIENT CONDITION

Vibration resistance:	5g f= 2...500Hz (EN-IEC 60068-2-6)
IK front protection:	IK04
Climate resistance:	+25°C-97%RH / +45°C-93%RH (IEC-EN60068-2-30)
Operating temperature:	– 25 °C ... + 55 °C
IP front protection:	IP65
Shock resistance:	30g, 18ms (EN-IEC 60068-2-27) 50g, 11ms (EN-IEC 60068-2-27)


CERTIFICATE

Standards:	CSA C22-2, IEC EN 60947-1, IEC EN 60947-5-1, UL508
Conformities:	CE
Approbations:	CSA, UL

OTHER

Housing colour:	Black
max. number of switching elements:	4
Housing material:	Plastic
Short Description:	Actuator, Ø 30.5 mm, Ø 35 mm, illuminative, Red, short, round, Silver, Aluminium, Maintained - Maintained, IP65, IK04
Switching positions:	

Dimension drawings:



Mounting cut-outs:

