

# POSAC-C13AS/NZS18 series

AC Power Cable



## model

### POSAC-C13AS/NZS18

AC Power Cable with NZS312 plug & C13 plug, 1.8m long

## mechanical specification

|                                  |                                                  |
|----------------------------------|--------------------------------------------------|
| connector type (output)          | IEC-C13                                          |
| connector type (input)           | NZS312                                           |
| length                           | 1800mm                                           |
| core area                        | 3x0.75mm <sup>2</sup>                            |
| wire construction                | pure copper core, flexible, multiwire conductors |
| insulation material              | PVC                                              |
| inner conductor                  | Cu                                               |
| external dimensions of the cable | 5.8 mm                                           |
| color of the cores               | black                                            |

## electrical specification

|                       |                 |
|-----------------------|-----------------|
| nominal voltage       | 0 - 500VAC      |
| rated current         | 7.5A            |
| Insulation resistance | >100MΩ @ 500VAC |
| Insulation thickness  | 0.5mm / 0.6mm   |
| Wire resistance       | max 0.044Ω/m    |
| Working Temperature   | -40°C ÷ 70°C    |

## safety

|      |                |
|------|----------------|
| RoHS | RoHS 2015/863  |
| LVD  | LVD 2014/35/UE |

# POSAC-C13AS/NZS18 series

AC Power Cable



## mechanical specification

