





ROCKER SWITCH MODEL:MR SERIES
RATING:12(4)A 125/250V~T55(cURus / ENEC15)
10(4)A 250V~ T125/55 (CQC)
DIELECTRIC WITHSTAND VOLTAGE:1500VAC FOR 1 MINUTE
INSULATION RESISTANCE:500VDC 100MΩ (MIN.)
CONTACT RESISTANCE: 20mΩ INITIAL (MAX.)



X(PANEL THICKNESS)	Y(CUTOUT DIMENSION)	Z(CUTOUT DIMENSION)
0.75~1.25mm	19.2 ^{+0.1} ₀ mm	12.90 ^{+0.15} ₀ mm
1.25~2 mm	19.4 ^{+0.1} ₀ mm	12.90 ^{+0.15} ₀ mm
2~3 mm	19.8 ^{+0.1} ₀ mm	12.90 ^{+0.15} ₀ mm

PANEL CUTOUT DIMENSION TABLE

NOTE: TOLERANCES UNLESS OTHERWISE SPECIFIED:±.012/0.3 (in/mm)

REVISION	DESCRIPTION	REVISED BY	TOLERANCES		ANGLE 1/2°	SCALE	UNIT	PART NAME	MR SPEC DRAWING	DWG NO
△1			DRAWN BY	周俊	DESIGNED BY	邹红海	5/3			
△3			CHECKED BY	周俊	APPROVED BY	邹红海				
△2										
△	2024.08.27	首次出圖		周俊			2024.08.27	PART NO	MR-211C5W-NBBP-18GC	S9992A