



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 17.01.2023

Version number 2.4 (replaces version 2.3)

Revision: 17.01.2023

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

- Trade name: Loetdraht Kristall 400 Ecoloy TC
Loetdraht Kristall 400 Ecoloy TC300

Loetdraht Kristall 400 Flowtin TC
Loetdraht Kristall 400 Flowtin TC300

1.2 Relevant identified uses of the substance or mixture and uses advised against

- Technical function soldering
- Application of the substance / the mixture Brazing alloy

1.3 Details of the supplier of the safety data sheet

Manufacturer/Supplier:
Stannol GmbH & Co. KG
Haberstrasse 24
D-42551 Velbert

Supplier: Transfer Multisort Elektronik Ltd.
Coleshill, Birmingham Coleshill House Suite 1C, 1 Station Road
+44 1675790026 e-mail: office@tme-uk.eu

+49 (0) 2051 3120 332
sdb@stannol.de

- Further information obtainable from: Product Safety Department

- 1.4 Emergency telephone number:
8:00 am - 5:00 pm (CET) +49 (0) 2051 3120 332

National Poisons Information Service
+44 121 507 4123

Members of the public seeking specific information on poisons should contact:
In England and Wales: NHS 111 - dial 111
In Scotland: NHS 24 - dial 111

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

- Classification according to Regulation (EC) No 1272/2008
The product is not classified, according to the GB CLP regulation.

2.2 Label elements

- Labelling according to Regulation (EC) No 1272/2008 Does not meet labeling criteria
- Hazard pictograms Void
- Signal word Void
- Hazard statements Void

2.3 Other hazards

Solder wires / solder pastes:

Inhalation of vapors released during the soldering process should be avoided. Flux vapors irritate the nose, throat, and respiratory tract, and can lead to allergic reactions (asthma) after prolonged or repeated contact. Therefore, an active suction is recommended.

After working with the product and before eating, drinking or smoking, wash your hands with soap and water.

Do not heat above 500 °C.

Keep out of the reach of children.

- Results of PBT and vPvB assessment

- PBT: Not applicable.
- vPvB: Not applicable.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

- Description: Mixture of substances listed below with nonhazardous additions.

(Contd. on page 2)
GB



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 17.01.2023

Version number 2.4 (replaces version 2.3)

Revision: 17.01.2023

Trade name: Loetdraht Kristall 400 Ecoloy TC
Loetdraht Kristall 400 Ecoloy TC300
Loetdraht Kristall 400 Flowtin TC
Loetdraht Kristall 400 Flowtin TC300

(Contd. of page 1)

· **Dangerous components:**

CAS: 7440-50-8 Copper, solid
EINECS: 231-159-6

substance with a Community workplace exposure limit 0.5 - 4%

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

· **4.1 Description of first aid measures**

- **General information:** No special measures required.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:** Rinse opened eye for several minutes under running water.
- **After swallowing:** If symptoms persist consult doctor.
- **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.
- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Ensure adequate ventilation
Wear protective clothing.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:** Pick up mechanically.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** No special measures required.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** None.
- **Storage class:** 11
- **7.3 Specific end use(s)** No further relevant information available.



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 17.01.2023

Version number 2.4 (replaces version 2.3)

Revision: 17.01.2023

Trade name: Loetdraht Kristall 400 Ecoloy TC
Loetdraht Kristall 400 Ecoloy TC300
Loetdraht Kristall 400 Flowtin TC
Loetdraht Kristall 400 Flowtin TC300

(Contd. of page 2)

SECTION 8: Exposure controls/personal protection

- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**
CAS: 7440-50-8 Copper, solid
WEL (Great Britain) Short-term value: 2** mg/m³
Long-term value: 0.2* 1** mg/m³
*fume **dusts and mists (as Cu)
- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Appropriate engineering controls** No further data; see item 7.
- **Individual protection measures, such as personal protective equipment**
- **General protective and hygienic measures:**
The usual precautionary measures are to be adhered to when handling chemicals.
- **Respiratory protection:**
Not necessary if room is well-ventilated.
Use suitable respiratory protective device in case of insufficient ventilation.
Filter A/P2
- **Hand protection**



Protective gloves

Rubber gloves

Synthetic rubber gloves

To avoid skin problems reduce the wearing of gloves to the required minimum.

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves**
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**
The determined penetration times according to EN 16523-1:2015 are not performed under practical conditions. Therefore a maximum wearing time, which corresponds to 50% of the penetration time, is recommended. The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye/face protection** Safety glasses

SECTION 9: Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**
- **General Information**
- **Physical state** Solid
- **Colour:** Grey
- **Odour:** Odourless
- **Odour threshold:** Not determined.
- **Melting point/freezing point:** Undetermined.
- **Boiling point or initial boiling point and boiling range** Undetermined.
- **Flammability** Not determined.

(Contd. on page 4)
GB



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 17.01.2023

Version number 2.4 (replaces version 2.3)

Revision: 17.01.2023

Trade name: Loetdraht Kristall 400 Ecoloy TC
Loetdraht Kristall 400 Ecoloy TC300
Loetdraht Kristall 400 Flowtin TC
Loetdraht Kristall 400 Flowtin TC300

(Contd. of page 3)

· Lower and upper explosion limit	
· Lower:	Not determined.
· Upper:	Not determined.
· Flash point:	Not applicable.
· Decomposition temperature:	Not determined.
· pH	Not applicable.
· Viscosity:	
· Kinematic viscosity	Not applicable.
· Dynamic:	Not applicable.
· Solubility	
· water:	Insoluble.
· Partition coefficient n-octanol/water (log value)	Not determined.
· Vapour pressure:	Not applicable.
· Density and/or relative density	
· Density:	Not determined.
· Relative density	Not determined.
· Vapour density	Not applicable.
· 9.2 Other information	
· Appearance:	
· Form:	Wire
· Important information on protection of health and environment, and on safety.	
· Auto-ignition temperature:	Product is not selfigniting.
· Explosive properties:	Product does not present an explosion hazard.
· Solvent content:	
· Solids content:	100.0 %
· Change in condition	
· Evaporation rate	Not applicable.
· Information with regard to physical hazard classes	
· Explosives	Void
· Flammable gases	Void
· Aerosols	Void
· Oxidising gases	Void
· Gases under pressure	Void
· Flammable liquids	Void
· Flammable solids	Void
· Self-reactive substances and mixtures	Void
· Pyrophoric liquids	Void
· Pyrophoric solids	Void
· Self-heating substances and mixtures	Void
· Substances and mixtures, which emit flammable gases in contact with water	Void
· Oxidising liquids	Void
· Oxidising solids	Void
· Organic peroxides	Void
· Corrosive to metals	Void
· Desensitised explosives	Void

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.

(Contd. on page 5)
GB



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 17.01.2023

Version number 2.4 (replaces version 2.3)

Revision: 17.01.2023

Trade name: Loetdraht Kristall 400 Ecoloy TC
Loetdraht Kristall 400 Ecoloy TC300
Loetdraht Kristall 400 Flowtin TC
Loetdraht Kristall 400 Flowtin TC300

(Contd. of page 4)

- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.
- **11.2 Information on other hazards**
- **Endocrine disrupting properties**
None of the ingredients is listed.

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Endocrine disrupting properties** The product does not contain substances with endocrine disrupting properties.
- **12.7 Other adverse effects**
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation** Smaller quantities can be disposed of with household waste.
- **Uncleaned packaging:**
- **Recommendation:** Packagings that may not be cleansed are to be disposed of in the same manner as the product.

GB
(Contd. on page 6)



Safety data sheet according to 1907/2006/EC, Article 31

Printing date 17.01.2023

Version number 2.4 (replaces version 2.3)

Revision: 17.01.2023

Trade name: Loetdraht Kristall 400 Ecoloy TC
Loetdraht Kristall 400 Ecoloy TC300
Loetdraht Kristall 400 Flowtin TC
Loetdraht Kristall 400 Flowtin TC300

(Contd. of page 5)

SECTION 14: Transport information

- **14.1 UN number or ID number**
- **ADR, ADN, IMDG, IATA** not regulated
- **14.2 UN proper shipping name**
- **ADR, ADN, IMDG, IATA** not regulated
- **14.3 Transport hazard class(es)**
- **ADR, ADN, IMDG, IATA**
- **Class** not regulated
- **14.4 Packing group**
- **ADR, IMDG, IATA** not regulated
- **14.5 Environmental hazards:** Not applicable.
- **14.6 Special precautions for user** Not applicable.
- **14.7 Maritime transport in bulk according to IMO instruments** Not applicable.
- **UN "Model Regulation":** not regulated

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Labelling according to Regulation (EC) No 1272/2008** Void
- **Hazard pictograms** Void
- **Signal word** Void
- **Hazard statements** Void
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Department issuing SDS:** Product Safety Department
- **Contact:** Hr. Dörr
- **Abbreviations and acronyms:**
 - ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)
 - IMDG: International Maritime Code for Dangerous Goods
 - IATA: International Air Transport Association
 - GHS: Globally Harmonised System of Classification and Labelling of Chemicals
 - EINECS: European Inventory of Existing Commercial Chemical Substances
 - ELINCS: European List of Notified Chemical Substances
 - CAS: Chemical Abstracts Service (division of the American Chemical Society)
 - PBT: Persistent, Bioaccumulative and Toxic
 - vPvB: very Persistent and very Bioaccumulative