


IE5238



Inductive sensor

IEA2002-FRKG/PH



Product characteristics

Electrical design	PNP/NPN
Output function	normally open / normally closed; (selectable)
Sensing range [mm]	2
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 50

Electrical data

Operating voltage [V]	5...36 DC
Protection class	III

Outputs

Electrical design	PNP/NPN
Output function	normally open / normally closed; (selectable)
Max. voltage drop switching output DC [V]	4.6
Minimum load current [mA]	4
Max. leakage current [mA]	0.8
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	2000
Short-circuit protection	yes
Overload protection	yes

Detection zone

Sensing range [mm]	2
Real sensing range S_r [mm]	$2 \pm 10\%$
Operating distance [mm]	0...1.6

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis [% of Sr]	1...15
Switch point drift [% of Sr]	-10...10

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

IE5238



Inductive sensor

IEA2002-FRKG/PH

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
MTTF	[years]	3377

Mechanical data		
Weight	[g]	49.9
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M8 x 1 / L = 50
Thread designation		M8 x 1
Materials		brass white bronze coated; sensing face: POM; end cap: PC
Tightening torque	[Nm]	A = 5 mm: 1 Nm; B: 2 Nm

Displays / operating elements		
Display	switching status	1 x LED, yellow



Accessories		
Items supplied		lock nuts: 2

Remarks		
Pack quantity		1 pcs.

Electrical connection		
-----------------------	--	--

Cable: 2 m, PUR / PVC; 2 x 0.14 mm²

Connection		
------------	--	--



BK = Core colours :
black
WH = white

IE5238

Inductive sensor

IEA2002-FRKG/PH



Diagrams and graphs

Installation

