


Fibre optic through-beam sensor

FE-11-EPA-M4/F1X1/2M



Application

Function principle

Through-beam sensor

Application

For use in industrial environments

Detection zone

Range with fibre-optic
amplifier type

OB50; OBF; OCF; OO50

OB50

Range of fibre optics

[mm]

200

OBF

Range of fibre optics

[mm]

450

OCF (High Power)

Range of fibre optics

[mm]

2800

OO50

Range of fibre optics

[mm]

800

Operating conditions

Ambient temperature

[°C]

-40...70

Mechanical data

Weight

[g]

47.5

Version of sensing head

straight

Sensing head thread

M4

E20606



Fibre optic through-beam sensor

FE-11-EPA-M4/F1X1/2M

Sensing head length	[mm]	15
Total length	[mm]	2000
Min. bending radius	[mm]	30
Fibre arrangement		
Core diameter	[mm]	1
Fibre material		PMMA
Fibre head material		aluminium
Fibre sheath material		PE
Accessories		
Items supplied		hexagon nuts: 4 x M4
		tooth lock washers: 4
Accessories (optional)		Cutter for fibre optics:, E20600
Remarks		
Pack quantity		1 pcs.